



REV. A	DESCRIPTION NEW DRAWING	DATE 2/22/2008
-----------	----------------------------	-------------------



SCALE: 3:1



TOLERANCE:
X.X ±0.2mm
X.XX ±0.1mm
X.XXX ±0.05mm



CUI INC

20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

TITLE: 2.5mm AUDIO JACK-MONO

REV: A


PART NO: MJ-2507

UNITS: MM [INCHES]

APPROVED BY: ZRJ

SCALE: 4:1

SPECIFICATIONS:
 RATING: 12V DC @ 1A
 CONTACT RESISTANCE: 30m OHMS MAX
 INSULATION RESISTANCE: 50M OHMS MIN: 100V DC
 VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
 LIFE: 5,000 CYCLES
 OPERATING TEMP: -25° ~ +85°C

MODEL NO.	MJ-2507
DIA.	THREADED
	M4X0.5
SCHEMATIC	

TERMINAL 1	MATERIAL	PLATING
TERMINAL 1	Brass	
TERMINAL 2	Copper Alloy	
TERMINAL 3	Brass	
BUSHING	Brass	
BODY	PBT	