



| | | |
|-----------|----------------------------|-------------------|
| REV. A | DESCRIPTION NEW DRAWING | DATE 2/22/2008 |
|-----------|----------------------------|-------------------|



TOLERANCE:
X.X ±0.2mm
X.XX ±0.1mm
X.XXX ±0.05mm

SCALE: 3:1





CUI INC

20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

TITLE: 2.5mm AUDIO JACK-MONO

REV: A


PART NO: MJ-2507

UNITS: MM [INCHES]

APPROVED BY: ZRJ

SCALE: 4:1

SPECIFICATIONS:
 RATING: 12V DC @ 1A
 CONTACT RESISTANCE: 30m OHMS MAX
 INSULATION RESISTANCE: 50M OHMS MIN: 100V DC
 VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
 LIFE: 5,000 CYCLES
 OPERATING TEMP: -25° ~ +85°C

| | |
|-----------|---|
| MODEL NO. | MJ-2507 |
| DIA. | THREADED M4X0.5 |
| SCHEMATIC |  |

| TERMINAL 1 | MATERIAL | PLATING |
|------------|--------------|---------|
| TERMINAL 1 | Brass | |
| TERMINAL 2 | Copper Alloy | |
| TERMINAL 3 | Brass | |
| BUSHING | Brass | |
| BODY | PBT | |