






| REV. | DESCRIPTION | DATE |
|------|--------------------|-----------|
| A | NEW DRAWING | 1/27/2006 |
| B | Updated PCB layout | 4/19/2006 |




PCB LAYOUT
TOP VIEW



TOLERANCE:
±0.3mm UNLESS OTHERWISE
SPECIFIED



SPECIFICATIONS:
 RATING: 12V DC @ 1A
 CONTACT RESISTANCE: 10~20m OHMS MAX
 INSULATION RESISTANCE: 50M OHMS MIN: 500V DC
 VOLTAGE WITHSTAND: 250V AC R.M.S. FOR 1 MINUTE
 LIFE: 10,000 CYCLES



| | MATERIAL | PLATING |
|------------|-----------------|---------|
| TERMINAL 1 | Tin Bronze | Silver |
| TERMINAL 2 | Copper Titanium | Silver |
| TERMINAL 3 | Brass | Silver |
| TERMINAL 4 | Brass | Silver |
| TERMINAL 5 | Copper Titanium | Silver |
| HOUSING | PBT | |



9615 SW Allen Blvd., Ste. 103
 Beaverton, OR 97005
 Phone: 503-643-4899
 800-275-4899
 Fax: 503-372-1266
 Website: www.cui.com

| | |
|----------------------------------|--------------------|
| TITLE: 3.5mm AUDIO JACK - STEREO | REV: B |
| PART NO. SJ-3505 | UNITS: MM [INCHES] |
| DRAWN BY: ZRJ | APPROVED BY: |
| | SCALE: 3:1 |

PC FILE NAME:
SJ-3505

COPYRIGHT 2006 BY CUI INC.