



REV.	DESCRIPTION	DATE
A	NEW DRAWING	11/03/2010



CONNECTOR PINOUT				
#	COLOR	AMT203	AMT303	AMT303LD
14	ORN/WHI	T_Bit	GND_C	GND_C
13	BLU/WHI	N/A	N/A	-X
12	WHI/BLU	X	X	X
11	GRN/WHI	N/A	N/A	-A
10	WHI/GRN	A	A	A
9	YLW/WHI	N/A	N/A	-B
8	WHI/YLW	B	B	B
7	WHI/ORN	MOSI	V	V
6	PNK/WHI	5 V+	5 V+	5 V+
5	BRN/WHI	SCK	W	W
4	WHI/PNK	GND	GND	GND
3	TAN/WHI	MISO	U	U
2	WHI/BRN	CSB	zero set	zero set
1	WHI/TAN	N/A	N/A	N/A

AMT203303- XX X X XXX

Terminated conductor count:
10C = 10 (AMT203/303)
14C = 14 (AMT303LD)

Length:
(in inches)

Temperature rating:
S = standard (80°C)
H = high (105°C)

Connector:
"blank" = standard
L = locking

TOLERANCE:
±0.3mm UNLESS OTHERWISE
SPECIFIED



20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

TITLE: AMT203/303 Interface Cable		REV: A
PART NO: AMT203303-XXCXXXXX	UNITS: MM [INCHES]	
DRAWN BY: JRH	APPROVED BY:	SCALE: 2:1