

**PART NUMBER:** CS-3603


**DESCRIPTION:** solid state buzzer

**SPECIFICATONS**

operating voltage	2 ~ 4 V DC	
current consumption	50 mA max.	at 3 V DC
sound pressure level	75 db min.	at 30 cm/3 V DC
tone	continuous	
operating temperature	-20 ~ +60° C	
storage temperature	-30 ~ +70° C	
weight	9.7 g max.	
RoHS	yes	

**APPEARANCE DRAWING**

tolerance:  $\pm 0.5$   
units: mm



**CURRENT CONSUMPTION/SOUND PRESSURE LEVEL**

