


REV. A	DESCRIPTION NEW DRAWING	DATE 2/22/2008
-----------	----------------------------	-------------------



SCALE: 3:1



TOLERANCE:
X.X ±0.2mm
X.XX ±0.1mm
X.XXX ±0.05mm



20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

SPECIFICATIONS:
RATING: 12V DC @ 1A
CONTACT RESISTANCE: 30m OHMS MAX
INSULATION RESISTANCE: 50M OHMS MIN: 100V DC
VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
LIFE: 5,000 CYCLES
OPERATING TEMP: -25° ~ +85°C

MODEL NO.	MJ-2507
DIA.	THREADED
	M4X0.5
SCHEMATIC	

TITLE:	2.5mm AUDIO JACK-MONO	REV:	A
PART NO.	MJ-2507	UNITS:	MM [INCHES]
DRAWN BY:	ZRJ	APPROVED BY:	
		SCALE:	4:1

TERMINAL 1	MATERIAL	PLATING
TERMINAL 1	Brass	
TERMINAL 2	Copper Alloy	
TERMINAL 3	Brass	
BUSHING	Brass	
BODY	PBT	