


| | | |
|-----------|----------------------------|-------------------|
| REV. A | DESCRIPTION NEW DRAWING | DATE 2/22/2008 |
|-----------|----------------------------|-------------------|



SCALE: 3:1



TOLERANCE:
X.X ±0.2mm
X.XX ±0.1mm
X.XXX ±0.05mm



20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

SPECIFICATIONS:
RATING: 12V DC @ 1A
CONTACT RESISTANCE: 30m OHMS MAX
INSULATION RESISTANCE: 50M OHMS MIN: 100V DC
VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
LIFE: 5,000 CYCLES
OPERATING TEMP: -25° ~ +85°C

| TERMINAL | MATERIAL | PLATING |
|------------|--------------|---------|
| TERMINAL 1 | Brass | |
| TERMINAL 2 | Copper Alloy | |
| TERMINAL 3 | Brass | |
| BUSHING | Brass | |
| BODY | PBT | |

| | |
|-----------|--------------------|
| MODEL NO. | MJ-2507N |
| DIA. | NON-THREAD Ø4.0 |
| SCHEMATIC | |

| | | | |
|-----------|-----------------------|--------------|-------------|
| TITLE: | 2.5mm AUDIO JACK-MONO | REV: | A |
| PART NO. | MJ-2507N | UNITS: | MM [INCHES] |
| DRAWN BY: | ZRJ | APPROVED BY: | |
| | | SCALE: | 4:1 |