




| | | |
|------|-------------|------------|
| REV. | DESCRIPTION | DATE |
| A | NEW DRAWING | 11/15/2005 |



| | |
|-----------|--------------------|
| MODEL NO. | MJ-2508 |
| D DIA. | THREADED M4X0.5 |
| SCHEMATIC | |

SPECIFICATIONS:
 RATING: 12V DC @ 1A
 CONTACT RESISTANCE: 30m OHMS MAX
 INSULATION RESISTANCE: 50M OHMS MIN: 100V DC
 VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
 LIFE: 5,000 CYCLES
 OPERATING TEMP: -25° ~ +85°C

| | MATERIAL | PLATING |
|------------|--------------|---------|
| BUSHING | Brass | Nickel |
| TERMINAL 1 | Brass | Tin |
| TERMINAL 2 | Copper Alloy | Tin |
| TERMINAL 3 | Brass | Tin |
| HOUSING | PBT | |



TOLERANCE:
 X.X ±0.2mm
 X.XX ±0.1mm
 X.XXX ±0.05mm



CUI INC

20050 SW 112th Ave.
 Tualatin, OR 97062
 Phone: 503-643-4899
 800-275-4899
 Fax: 503-372-1266
 Website: www.cui.com

| | | | |
|-----------|-----------------------|--------------|-------------|
| TITLE: | 2.5mm AUDIO JACK-MONO | REV: | A |
| PART NO: | MJ-2508 | UNITS: | MM [INCHES] |
| DRAWN BY: | ZRJ | APPROVED BY: | |
| | | SCALE: | 3:1 |