





|      |             |            |
|------|-------------|------------|
| REV. | DESCRIPTION | DATE       |
| A    | NEW DRAWING | 11/15/2005 |



TOLERANCE:  
 X.X ±0.2mm  
 X.XX ±0.1mm  
 X.XXX ±0.05mm



**CUI INC**

20050 SW 112th Ave.  
 Tualatin, OR 97062  
 Phone: 503-643-4899  
 800-275-4899  
 Fax: 503-372-1266  
 Website: www.cui.com

**SPECIFICATIONS:**  
 RATING: 12V DC @ 1A  
 CONTACT RESISTANCE: 30m OHMS MAX  
 INSULATION RESISTANCE: 50M OHMS MIN; 100V DC  
 VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE  
 LIFE: 5,000 CYCLES  
 OPERATING TEMP: -25° ~ +85°C

|           |                       |              |             |
|-----------|-----------------------|--------------|-------------|
| TITLE:    | 2.5mm AUDIO JACK-MONO | REV:         | A           |
| PART NO:  | MJ-2508N              | UNITS:       | MM [INCHES] |
| DRAWN BY: | ZRJ                   | APPROVED BY: |             |
|           |                       | SCALE:       | 3:1         |

| BUSHING    | MATERIAL     | PLATING |
|------------|--------------|---------|
| TERMINAL 1 | Brass        | Nickel  |
| TERMINAL 2 | Brass        | Tin     |
| TERMINAL 3 | Copper Alloy | Tin     |
| HOUSING    | Brass        | Tin     |
|            | PBT          |         |

|           |                    |
|-----------|--------------------|
| MODEL NO. | MJ-2508N           |
| D DIA.    | NON-THREAD<br>Ø4.0 |
| SCHEMATIC |                    |