



| REV. | DESCRIPTION | DATE |
|------|-----------------------|------------|
| A | NEW DRAWING | 9/8/2008 |
| B | CORRECTED RATING TYPO | 01/09/2015 |



TOLERANCE:
±0.3mm
UNLESS OTHERWISE SPECIFIED



△ SPECIFICATIONS:
 RATING: 16VDC @ 20mA~0.3A
 CONTACT RESISTANCE: 50m OHMS MAX
 INSULATION RESISTANCE: 100M OHMS MIN: 500V DC
 VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
 LIFE: 5,000 CYCLES



| | MATERIAL | PLATING |
|------------|--------------|---------|
| HEX NUT | Steel | Nickel |
| TERMINAL 1 | Copper Alloy | Gold |
| TERMINAL 2 | Copper Alloy | Nickel |
| TERMINAL 3 | Copper Alloy | Nickel |
| TERMINAL 4 | Copper Alloy | Nickel |
| SHELL | Brass | Nickel |
| HOUSING | PBT | |

CUI INC

20050 SW 112th Ave.
 Tualatin, OR 97062
 Phone: 503-612-2300
 800-275-4899
 Fax: 503-612-2383
 Website: www.cui.com

| | | |
|---|--------------|--------------------|
| TITLE: 3.5mm Panel Mount Audio Jack - 4 Connector | | REV: B |
| PART NO. SJ5-43502PM | | UNITS: MM [INCHES] |
| DRAWN BY: RDS | APPROVED BY: | SCALE: 3:1 |

PC FILE NAME:
SJ5-43502PM

COPYRIGHT 2008 BY CUI INC.