






| REV. | DESCRIPTION | DATE |
|------|------------------------|-----------|
| A | NEW DRAWING | 7/17/2006 |
| B | pin schematic added | 12/5/2006 |
| C | added pin designations | 9/2/2008 |
| D | corrected thread size | 1/30/2014 |



HOUSING DETAIL DRAWING

TOLERANCE:
±0.3mm UNLESS OTHERWISE
SPECIFIED



| | |
|-----------|---------|
| MODEL NO. | SR-2501 |
| SCHMATIC | |

SPECIFICATIONS:
 CONTACT RESISTANCE: 50m OHMS MAX
 INSULATION RESISTANCE: 100M OHMS MIN: 500V DC
 VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
 LIFE: 5,000 CYCLES

| | MATERIAL | PLATING |
|------------|-----------------|---------|
| TERMINAL 1 | Brass | Nickel |
| TERMINAL 2 | Phosphor Bronze | Nickel |
| TERMINAL 3 | Phosphor Bronze | Gold |
| INSULATOR | Brass | Gold |
| CAP | PE | |
| HOUSING | PA | |



20050 SW 112th Ave.
 Tualatin, OR 97062
 Phone: 503-612-2300
 800-275-4899
 Fax: 503-612-2383
 Website: www.cui.com

| | | |
|----------------------------|--------------|--------------------|
| TITLE: IN-LINE STEREO JACK | | REV: D |
| PART NO. SR-2501 | | UNITS: MM [INCHES] |
| DRAWN BY: RDS | APPROVED BY: | SCALE: 2:1 |

PC FILE NAME:
SR-2501

COPYRIGHT 2008 BY CUI INC.