

SERIES: AE15-UW | **DESCRIPTION:** DC-DC CONVERTER

FEATURES


- 15 watts
- high operating temp -40 to +70°C
- 4,000 Vac isolation
- UL 1741 approved; EN 62109 approved
- board mounted
- input voltage range of 200~1,500 Vdc
- low ripple & noise
- OVP protection
- output short circuit protection



MODEL	input voltage range (Vdc)	output voltage (Vdc)	output current		output power max (W)	ripple & noise ¹ max (mVp-p)	efficiency ² typ (%)
			min (A)	max (A)			
AE15-UW-S12	200~1500	12	0	1.25	15	300	71
AE15-UW-S15	200~1500	15	0	1.00	15	300	72
AE15-UW-S24	200~1500	24	0	0.625	15	300	74

Notes: 1. Measured at nominal input, 20 MHz bandwidth oscilloscope, with 10 µF electrolytic and 1 µF ceramic capacitors on the output.
 2. Measured at 800 Vdc input voltage, full load.
 3. All specifications are measured at Ta=25°C, humidity < 75%, nominal input voltage, and rated output load unless otherwise specified.

PART NUMBER KEY



INPUT

parameter	conditions/description	min	typ	max	units
operating input voltage		200		1500	Vdc
under voltage shutdown	shut-down range	170		185	Vdc
	turn-on range	180		195	Vdc
current	at 200 Vdc			120	mA
	at 800 Vdc			30	mA
	at 1500 Vdc			16	mA
inrush current	at 200 Vdc		30		A
	at 800 Vdc		80		A
	at 1500 Vdc		150		A
input fuse	15 A / 1500 Vdc (external)				

OUTPUT

parameter	conditions/description	min	typ	max	units
maximum capacitive load	12 Vdc output model			2,000	μ F
	15 Vdc output model			1,200	μ F
	24 Vdc output model			470	μ F
voltage accuracy			± 2		%
line regulation	from low line to high line, full load		± 1		%
load regulation	from 0% to full load		± 1		%
delay time	from $V_{in} = 0$ V to 90% of rated output voltage			2	s
switching frequency			65		kHz
temperature coefficient	at full load		± 0.02		%/ $^{\circ}$ C

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	12 Vdc, 15 Vdc output models			20	Vdc
	24 Vdc output model			30	Vdc
over current protection	automatic recovery	120		320	%
short circuit protection	continuous, automatic recovery				

SAFETY AND COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output for 1 minute	4,000			Vac
safety approvals	CSA (UL 1741), EN 62109				
conducted emissions	CISPR22/EN55022, class A (external circuit required, see Figure 2)				
radiated emissions	CISPR22/EN55022, class A (external circuit required, see Figure 2)				
ESD	IEC/EN61000-4-2, contact ± 6 kV/air ± 8 kV, class B				
radiated immunity	IEC/EN61000-4-3, 10V/m, class A				
EFT/burst	IEC/EN61000-4-4, ± 2 kV, class B (external circuit required, see Figure 2)				
surge	IEC/EN61000-4-5, line-line ± 1 kV, class B (external circuit required, see Figure 2)				
conducted immunity	IEC/EN61000-4-6, 10 Vr.m.s, class A				
magnetic field immunity	IEC/EN61000-4-8, 10 A/m, class A				
MTBF	as per MIL-HDBK-217F, 25 $^{\circ}$ C	300,000			hours
RoHS	2011/65/EU				

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature	see derating curves	-40		70	°C
storage temperature		-40		85	°C
storage humidity	non-condensing			95	%
altitude	see derating curves			5000	m

SOLDERABILITY

parameter	conditions/description	min	typ	max	units
hand soldering	for 3~5 seconds	350	360	370	°C
wave soldering	for 5~10 seconds	255	260	265	°C




MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	125.00 x 75.00 x 40.00 [4.921 x 2.953 x 1.575 inch]				mm
case material	black flame-retardant heat-proof plastic (UL94V-0)				
weight			300		g

MECHANICAL DRAWING

units: mm [inch]
 tolerance: ± 0.50 [± 0.020]
 pin diameter tolerance: ± 0.10 [± 0.004]
 pin height tolerance: ± 1.50 [± 0.059]

In high vibration environments, this series should be mounted with screws.
 tightening torque: max 0.4 N*m



Note : Grid 2.54*2.54mm


Recommended PCB Layout
 Top View

PIN CONNECTIONS	
PIN	Function
1	-Vin
2	+Vin
3	NC
4	-Vout
5	+Vout


NC=no connection

DERATING CURVES


12, 15 Vdc Output Models, Temperature Derating Curve
(200~300 Vdc input voltage)




24 Vdc Output Model, Temperature Derating Curve
(200~300 Vdc input voltage)




Temperature Derating Curve
(300~1500 Vdc input voltage)



Load vs. Input Voltage Derating Curve
(at 25°C)




Load vs. Altitude Derating Curve




EFFICIENCY CURVES


AE15-UW-S12 Efficiency Curve
Efficiency vs. Input Voltage




AE15-UW-S12 Efficiency Curve
Efficiency vs. Load Current




AE15-UW-S15 Efficiency Curve
Efficiency vs. Input Voltage




AE15-UW-S15 Efficiency Curve
Efficiency vs. Load Current



AE15-UW-S24 Efficiency Curve
Efficiency vs. Input Voltage



AE15-UW-S24 Efficiency Curve
Efficiency vs. Load Current



APPLICATION CIRCUIT




Table 1

Vout (Vdc)	Fuse	C1 (μF)	C2 (μF)	TVS
12	15 A / 1500 Vdc	1	120	SMBJ20A
15	15 A / 1500 Vdc	1	120	SMBJ20A
24	15 A / 1500 Vdc	1	68	SMBJ30A

EMC RECOMMENDED CIRCUIT

Figure 2




Table 2

Recommended External Circuit Components	
FUSE	15 A/1500 Vdc
C7, C8, C9, C10	104K/275 Vac
C3, C4, C5, C6	47 μF/450 Vdc
R1, R2, R3, R4	1 MΩ/2 W
LDM	330 μH/1 A
LCM	7 mH/1 A

Note: See also Table 1.

- Notes:
1. C1 is a ceramic capacitor used to filter high frequency noise.
 2. C2 is electrolytic and is recommended to be high frequency and low resistance. For capacitance and current of the capacitor, refer to the datasheet provided by the manufacturer. Capacitance withstand voltage derating should be 80% or above.

REVISION HISTORY

rev.	description	date
1.0	initial release	09/13/2017

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC[®]

Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.