


Efficiency Standards for External Power Supplies



The global regulatory environment surrounding the legislation of external power supply efficiency and no-load power draw has rapidly evolved over the past decade since the California Energy Commission (CEC) implemented the first mandatory standard in 2004. With the publication in 2014 of a new set of requirements by the United States Department of Energy (DoE) that went into effect in February 2016, the landscape has changed again as regulators further reduce the amount of energy that may be consumed by external power adapters.

Mandating higher average efficiencies in external power supplies has undoubtedly had a real impact on global power consumption. However, with the benefit of a reduced draw on the power grid come challenges and uncertainties for the electronics industry as it tries to keep up with this dynamic regulatory environment.

The next round of legislation is expected to come from Europe, as the current voluntary Code of Conduct (CoC) Tier 1 and Tier 2 standards are under review by the European Union to become compulsory as Ecodesign rules, with targeted implementation dates sometime in 2017 and 2018 respectively.

Original Equipment Manufacturers (OEMs) who design external power supplies into their products must continue to monitor the latest regulations to ensure that they are in compliance in each region where their product is sold. The goal of this paper is to provide an up-to-date summary of the most current regulations worldwide.

A BRIEF HISTORY

In the early 90's, it was estimated that there were more than one billion external power supplies active in the United States alone. The efficiency of these power supplies, mainly utilizing linear technology, could be as low as 50% and still draw power when the application was turned off or not even connected to the power supply (referred to as "no-load" condition). Experts calculated that without efforts to increase efficiencies and reduce "no-load" power consumption, external power supplies would account for around 30% of total energy consumption in less than 20 years. As early as 1992, the US Environmental Protection Agency started a voluntary program to promote energy efficiency and reduce pollution, which eventually became the Energy Star program. However, it was not until 2004 that the first mandatory regulation dictating efficiency and no-load power draw minimums was put in place. Figure 1 demonstrates just how dynamic the regulatory environment has been over the past decade. It also traces the path from the CEC's 2004 regulation up to the new DoE Level VI standards that went into effect in early 2016. It also shows the European Union's Code of Conduct standards that are voluntary now, but are currently under review to become Ecodesign requirements in two tiers. The Tier 1 standard, which is broadly equivalent to Level VI, is proposed to become mandatory sometime in 2017 and the tighter Tier 2 standard is proposed to become mandatory in 2018.




Figure 1: This infographic traces the path from the CEC's 2004 regulation up to the latest DoE Level VI standard, which became effective in February 2016, and also shows the EU roadmap for CoC and Ecodesign requirements.

THE CURRENT REGULATORY ENVIRONMENT

As different countries and regions enact stricter requirements and move from voluntary to mandatory programs, it has become vital that OEMs continually track the most recent developments to ensure compliance and avoid costly delays or fines. While many countries are establishing voluntary programs harmonized to the international efficiency marking protocol system first established by Energy Star, the following countries and regions now have regulations in place mandating that all external power supplies shipped across their borders meet the specified efficiency level:




Figure 2: This graphic shows the latest mandatory efficiency standard regulations by region.

Power supply manufacturers indicate compliance to these regulations by placing a Roman Numeral on the power supply label as specified by the International Efficiency Marking Protocol for External Power Supplies Version 3.0, updated in September 2013. This latest version of the Protocol provides additional flexibility on where the marking may be placed.

While the US is the only governing body to enforce compliance to the Level VI standard, most external power supply manufacturers have adjusted their product portfolios to meet these requirements. These adjustments are a direct response to the needs of OEM's to have a universally-compliant power supply platform for their products that ship globally. For similar reasons, manufacturers are also taking account of the latest EU CoC requirements to provide compliance ahead of these standards becoming mandatory Ecodesign rules.




Figure 3: Example of the International Efficiency Marking Protocol on a power supply label.

PERFORMANCE THRESHOLDS

Figure 4 summarizes the past performance thresholds established over time up to Level V. The internationally approved test method for determining efficiency has been published by the IEC as AS/NZS 4665 Part 1 and Part 2. The approach taken to establish an efficiency level is to measure the input and output power at 4 defined points: 25%, 50%, 75% and 100% of rated power output. Data for all 4 points are separately reported as well as an arithmetic average active efficiency across all 4 points.

Level	No-Load Power Requirement	Average Efficiency Requirement
I	used if you do not meet any of the criteria	
II	no criteria was ever established	no criteria was ever established
III	≤10 Watts: ≤0.5W of No Load Power 10~250 Watts: ≤0.75W No Load Power	≤1 Watt: ≥ Power x 0.49 1~49 Watts: ≥[0.09 x Ln(Power)] + 0.49 49~250 Watts: ≥84%
IV	0~250 Watts: ≤0.5W No Load Power	≤1 Watt: ≥ Power x 0.50 1~51 Watts: ≥[0.09 x Ln(Power)] + 0.5 51~250 Watts: ≥85%
V	Standard Voltage Ac-Dc Models (>6Vout)	
	0~49 Watts: ≤0.3W of No Load Power	≤1 Watt: 0.48 x Power + 0.140
	50~250 Watts: ≤0.5W of No Load Power	1~49 Watts: [0.0626 x Ln(Power)] + 0.622
		50~250 Watts: ≥87%
	Low Voltage Ac-Dc Models (<6Vout)	
	0~49 Watts: ≤0.3W of No Load Power	≤1 Watt: 0.497 x Power + 0.067
50~250 Watts: ≤0.5W of No Load Power	1~49 Watts: [0.0750 x Ln(Power)] + 0.561	
	50~250 Watts: ≥86%	

Figure 4: The table above summarizes past performance thresholds as they were established over time. The term "power" means the power designated on the label of the power supply.

DOE LEVEL VI

Power supply manufacturers such as CUI prepared well in advance for the transition to the more stringent Level VI standards. Along with tightened regulations for existing adapters, this standard expanded the range of regulated products. It should be noted that the current voluntary EU CoC Tier 1 requirements are broadly equivalent to DoE Level VI. However, there are differences in how the DoE and EU define external power supplies and the scope of which classes of supply are included or exempt from these rules. Regulated products now include:

- Multiple-voltage external power supplies
- Products with power levels >250 watts

The Level VI performance thresholds are summarized in the tables below:

Single-Voltage External Ac-Dc Power Supply ¹ , Basic-Voltage		
Nameplate Output Power (P _{out})	Minimum Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
P _{out} ≤ 1 W	$\geq 0.5 \times P_{out} + 0.16$	≤ 0.100
1 W < P _{out} ≤ 49 W	$\geq 0.071 \times \ln(P_{out}) - 0.0014 \times P_{out} + 0.67$	≤ 0.100
49 W < P _{out} ≤ 250 W	≥ 0.880	≤ 0.210
P _{out} > 250 W	≥ 0.875	≤ 0.500

Single-Voltage External Ac-Dc Power Supply, Low-Voltage ²		
Nameplate Output Power (P _{out})	Minimum Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
P _{out} ≤ 1 W	$\geq 0.517 \times P_{out} + 0.087$	≤ 0.100
1 W < P _{out} ≤ 49 W	$\geq 0.0834 \times \ln(P_{out}) - 0.0014 \times P_{out} + 0.609$	≤ 0.100
49 W < P _{out} ≤ 250 W	≥ 0.870	≤ 0.210
P _{out} > 250 W	≥ 0.875	≤ 0.500

Single-Voltage External Ac-Ac Power Supply, Low-Voltage		
Nameplate Output Power (P _{out})	Minimum Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
P _{out} ≤ 1 W	$\geq 0.517 \times P_{out} + 0.087$	≤ 0.210
1 W < P _{out} ≤ 49 W	$\geq 0.0834 \times \ln(P_{out}) - 0.0014 \times P_{out} + 0.609$	≤ 0.210
49 W < P _{out} ≤ 250 W	≥ 0.870	≤ 0.210
P _{out} > 250 W	≥ 0.875	≤ 0.500

Single-Voltage External Ac-Ac Power Supply ³ , Basic-Voltage		
Nameplate Output Power (P _{out})	Minimum Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
P _{out} ≤ 1 W	$\geq 0.5 \times P_{out} + 0.16$	≤ 0.210
1 W < P _{out} ≤ 49 W	$\geq 0.071 \times \ln(P_{out}) - 0.0014 \times P_{out} + 0.67$	≤ 0.210
49 W < P _{out} ≤ 250 W	≥ 0.880	≤ 0.210
P _{out} > 250 W	≥ 0.875	≤ 0.500

Multiple-Voltage External Power Supply ⁴		
Nameplate Output Power (P _{out})	Minimum Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
P _{out} ≤ 1 W	≥ 0.497 × P _{out} + 0.067	≤ 0.300
1 W < P _{out} ≤ 49 W	≥ 0.075 × ln(P _{out}) + 0.561	≤ 0.300
P _{out} > 49 W	≥ 0.860	≤ 0.300

Figure 5: The current US DoE Level VI efficiency requirements that became law in February 2016.

¹Single-Voltage External Ac-Dc Power Supply: An external power supply that is designed to convert line voltage ac into lower-voltage dc output and is able to convert to only one dc output voltage at a time.

²Low-Voltage External Power Supply: An external power supply with a nameplate output voltage less than 6 volts and nameplate output current greater than or equal to 550 milliamps. Basic-voltage external power supply means an external power supply that is not a low-voltage power supply.

³Single-Voltage External Ac-Ac Power Supply: An external power supply that is designed to convert line voltage ac into lower-voltage ac output and is able to convert to only one ac output voltage at a time.

⁴Multiple-Voltage External Power Supply: An external power supply that is designed to convert line voltage ac input into more than one simultaneous lower-voltage output.

DIRECT VS INDIRECT OPERATION EPSs

DoE Level VI also defines power supplies as direct operation and indirect operation products. A direct operation product is an external power supply (EPS) that functions in its end product without the assistance of a battery. An indirect operation EPS is not a battery charger but cannot operate the end product without the assistance of a battery. The new standard only applies to direct operation external power supplies. Indirect operation models will still be governed by the limits as defined by EISA2007. It is important to note that the current voluntary EU CoC Tier 1 and Tier 2 standards do not distinguish between direct and indirect operation. Figure 6 illustrates the instructions provided by the DoE to help distinguish between direct and indirect operation power supplies.

LEVEL VI EXEMPTIONS

The latest Level VI mandate also defines exemptions for EPS products. Direct operation EPS standards do not apply if:

- It is a device that requires Federal Food and Drug Administration listing and approval as a medical device in accordance with section 360c of title 21;

OR

- A direct operation, ac-dc external power supply with nameplate output voltage less than 3 volts and nameplate output current greater than or equal to 1,000 milliamps that charges the battery of a product that is fully or primarily motor-operated.




Figure 6: The instructions above have been provided by the DOE to help distinguish between direct and indirect operation power supplies.

VOLUNTARY EUROPEAN REQUIREMENTS

The European Union published its Code of Conduct (CoC) on Energy Efficiency of External Power Supplies Version 5 in October 2013. Tier 1 effectively harmonizes the EU with DoE Level VI, noting the differences in scope detailed below, and became effective as a voluntary requirement from January 2014, some two years ahead of DoE Level VI. Its adoption as an EU Ecodesign rule is currently under review and expected to be mandated sometime in 2017. The more stringent CoC Tier 2 requirement became effective on a voluntary basis from January 2016 and is similarly expected to become mandatory as an Ecodesign rule in 2018.

CoC Tier 1 Single-Voltage External Ac-Dc Power Supply, Basic-Voltage			
Nameplate Output Power (Pout)	Minimum Average Efficiency in Active Mode (expressed as a decimal)	10% Load Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
$0.3 \text{ W} \leq P_{out} \leq 1 \text{ W}$	$\geq 0.50 \times P_{out} + 0.146$	$\geq 0.50 \times P_{out} + 0.046$	≤ 0.150
$1 \text{ W} < P_{out} \leq 49 \text{ W}$	$\geq 0.0626 \times \ln(P_{out}) + 0.646$	$\geq 0.0626 \times \ln(P_{out}) + 0.546$	≤ 0.150
$49 \text{ W} < P_{out} \leq 250 \text{ W}$	≥ 0.890	≥ 0.790	≤ 0.250
$P_{out} > 250 \text{ W}$	N/A	N/A	N/A

CoC Tier 1 Single-Voltage External Ac-Dc Power Supply, Low-Voltage			
Nameplate Output Power (Pout)	Minimum Average Efficiency in Active Mode (expressed as a decimal)	10% Load Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
$0.3 \text{ W} \leq P_{out} \leq 1 \text{ W}$	$\geq 0.50 \times P_{out} + 0.086$	$\geq 0.50 \times P_{out}$	≤ 0.150
$1 \text{ W} < P_{out} \leq 49 \text{ W}$	$\geq 0.0755 \times \ln(P_{out}) + 0.586$	$\geq 0.072 \times \ln(P_{out}) + 0.50$	≤ 0.150
$49 \text{ W} < P_{out} \leq 250 \text{ W}$	≥ 0.880	≥ 0.780	≤ 0.250
$P_{out} > 250 \text{ W}$	N/A	N/A	N/A

Figure 7: The current EU CoC Tier 1 voluntary EPS efficiency requirements that are expected to become mandatory sometime in 2017.

The key difference between the CoC requirements and Level VI is the new 10% load measure, which imposes efficiency requirements under a low-load condition where historically most types of power supplies have been notoriously inefficient. As already noted, CoC does not distinguish between direct and indirect operation external power adapters. While CoC Tier 1 includes the new 10% load measure, its no-load and active mode limits are less stringent than DoE Level VI.

CoC Tier 2 further tightens the no-load and active mode power consumption limits for key classes of power adapters enacted by Level VI i.e. at output powers $\leq 49 \text{ W}$ and $49 \text{ W} < P_{out} \leq 250 \text{ W}$ and covers both standard voltage and low voltage adapters. The table in figure 8 details these and other new requirements.

LOOKING FORWARD

The Level VI requirements became effective on February 10, 2016, two years after their publication in the Federal Register. It is important to note that compliance with the DoE Level VI standard is regulated from the date of manufacture in the US or import into the US, so legacy products can still be shipped as long as existing power supplies meet these stipulations. Labeling requirements will be mandated to meet the same International Efficiency Marking Protocol for External Power Supplies Version 3.0 as the previous Level V standard.

Globally, it is expected that other nations will soon follow suit with the DoE Level VI standard. In the EU, the current voluntary CoC Tier 1 and Tier 2 requirements for external power supplies are expected to become mandatory European Ecodesign Directives, first essentially harmonizing with the US Level VI standard sometime in 2017 and then taking the lead with the more stringent Tier 2 rules in 2018. It should also be expected that countries with existing efficiency regulations previously in-line with the US, including Canada, will move to harmonize with these newer US and European standards.

CoC Tier 2 Single-Voltage External Ac-Dc Power Supply, Basic-Voltage			
Nameplate Output Power (Pout)	Minimum Average Efficiency in Active Mode (expressed as a decimal)	10% Load Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
$0.3 \text{ W} \leq P_{out} \leq 1 \text{ W}$	$\geq 0.50 \times P_{out} + 0.169$	$\geq 0.50 \times P_{out} + 0.060$	≤ 0.075
$1 \text{ W} < P_{out} \leq 49 \text{ W}$	$\geq 0.071 \times \ln(P_{out}) - 0.00115 \times P_{out} + 0.670$	$\geq 0.071 \times \ln(P_{out}) - 0.00115 \times P_{out} + 0.570$	≤ 0.075
$49 \text{ W} < P_{out} \leq 250 \text{ W}$	≥ 0.890	≥ 0.790	≤ 0.150
$P_{out} > 250 \text{ W}$	N/A	N/A	N/A

CoC Tier 2 Single-Voltage External Ac-Dc Power Supply, Low-Voltage			
Nameplate Output Power (Pout)	Minimum Average Efficiency in Active Mode (expressed as a decimal)	10% Load Average Efficiency in Active Mode (expressed as a decimal)	Maximum Power in No-Load Mode (W)
$0.3 \text{ W} \leq P_{out} \leq 1 \text{ W}$	$\geq 0.517 \times P_{out} + 0.091$	$\geq 0.517 \times P_{out}$	≤ 0.075
$1 \text{ W} < P_{out} \leq 49 \text{ W}$	$\geq 0.0834 \times \ln(P_{out}) - 0.0011 \times P_{out} + 0.609$	$\geq 0.0834 \times \ln(P_{out}) - 0.00127 \times P_{out} + 0.518$	≤ 0.075
$49 \text{ W} < P_{out} \leq 250 \text{ W}$	≥ 0.880	≥ 0.780	≤ 0.150
$P_{out} > 250 \text{ W}$	N/A	N/A	N/A

Figure 8: The current EU CoC Tier 2 voluntary EPS efficiency requirements that are expected to become mandatory in 2018.

SUMMARY

The EPA estimates that external power supply efficiency regulations implemented over the past decade have reduced energy consumption by 32 billion kilowatts, saving \$2.5 billion annually and reducing CO2 emissions by more than 24 million tons per year. Beyond the mandated government regulations, many OEMs are now starting to demand “greener” power supplies as a way to differentiate their end-products, driving efficiencies continually higher. In late 2014, CUI Inc began introducing DoE Level VI compliant adapters that now range from 3 W to 150 W. Recently, the company has further qualified the majority of its Level VI line to also conform to the more stringent CoC Tier 2 standards. Moving forward, CUI will continue to implement the latest energy saving technologies into its external power supplies in order to comply with current and future standards as the regulatory landscape continues to evolve.

