

**SERIES:** CP20 | **DESCRIPTION:** 2.0 A PELTIER MODULE

**FEATURES**


- solid state device
- small and lightweight
- precise temperature control
- quiet operation



MODEL	input voltage max (V)	input current max (A)	output Qmax <sup>1</sup>		output ΔTmax <sup>2</sup>	
			T <sub>h</sub> =27°C (W)	T <sub>h</sub> =50°C (W)	T <sub>h</sub> =27°C (°C)	T <sub>h</sub> =50°C (°C)
CP20151	3.8	2	3.7	4.0	66	72
CP20251	8.6	2	8.5	9.4	66	72
CP20351	15.4	2	15.2	16.9	66	72

Notes: 1. maximum cooling capacity at I<sub>max</sub>, V<sub>max</sub> and ΔT=0°C  
 2. maximum temperature difference at I<sub>max</sub>, V<sub>max</sub> and Q=0W (maximum parameters are measured in a vacuum)

**PART NUMBER KEY**




**GENERAL**


parameter	conditions/description	min	typ	max	units
internal resistance <sup>3</sup>	CP20151	1.44	1.6	1.76	Ω
	CP20251	3.33	3.7	4.07	Ω
	CP20351	6.03	6.7	7.37	Ω
solder melting temperature	connection between thermoelectric pairs			138	°C
assembly compression				98.07	N/cm <sup>2</sup>
				10	kgf/cm <sup>2</sup>
hot side plate				80	°C
MTBF				200,000	hours

Notes: 3. measured by AC 4-terminal method at 25°C


### CP20151 PERFORMANCE (Th=27°C)




### CP20151 PERFORMANCE (Th=50°C)




### CP20251 PERFORMANCE (Th=27°C)




### CP20251 PERFORMANCE (Th=50°C)



### CP20351 PERFORMANCE (Th=27°C)




### CP20351 PERFORMANCE (Th=50°C)





## MECHANICAL DRAWING

units: mm



	MATERIAL	PLATING
ceramic plate	Al <sub>2</sub> O <sub>3</sub> (Alumina)	
sealer	silicon rubber RTV	
lead wire	UL1430 (22AWG)	tin
joint cover	silicon rubber RTV	



MODEL	LENGTH x WIDTH (mm)
CP20151	15 x 15 ± 0.3
CP20251	20 x 20 ± 0.3
CP20351	30 x 30 ± 0.3

## REVISION HISTORY

rev.	description	date
1.0	initial release	09/03/2009
1.01	applied new template	05/07/2012

The revision history provided is for informational purposes only and is believed to be accurate.



**Headquarters**  
20050 SW 112th Ave.  
Tualatin, OR 97062  
**800.275.4899**

Fax 503.612.2383  
**cui.com**  
techsupport@cui.com

CUI offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.