



PART NUMBER: MEH30

DESCRIPTION: incremental encoder

ELECTRICAL SPECIFICATIONS

output waveform	Square Wave
output signals	A, B, Z phase
current consumption	≤50 mA
frequency response	0~100 KHz
output phase difference	A, B phase difference 90° ± 45° (T/4±T/8) Z phase T±T/2 (see output waveform)
supply voltage	5 V dc (Line driver output only), 5 V ~ 12 V dc ± 10%, 24 V dc ± 10% (open collector output only)
output resolution (ppr)	40, 50, 60, 100, 200, 250, 300, 360, 400, 450, 500, 512, 600, 720, 800, 900, 1000, 1024, 1200, 1500, 1800, 2000, 2048, 2500, 3600, 4500, 9000
waveform rise/fall time	2μ or less (output cable 1m or less)

MECHANICAL SPECIFICATIONS

max shaft load, radial:	19.6N (2kgf)	14.7N (1.5kgf) (800-9000 ppr)
axial:	9.8N (1kgf)	4.9N (0.5kgf) (800-9000 ppr)
starting torque	2 x 10 ⁻³ N·m (20 gf·cm)	
max rotational speed	6000 RPM	
shock resistance	500 m/s ² (50G), 3 times each on XYZ	
vibration proof	55 Hz, double amplitude 1.5mm, 2 hours each on XYZ	
weight	70g (with 1m cable)	
cable	4.2mm outside diameter, 5 core vinyl wire insulated shield cable (1m)	

ENVIRONMENTAL SPECIFICATIONS

operating temp	-10° to +70° C
storage temp	-20° to +80° C
humidity	RH 35%~90% non collecting

ORDERING INSTRUCTIONS

MEH30 - XXXXP-XX-XX-XX


Resolution (PPR):	Output Circuit:	Input Voltage:	Bore Size:	Bore/Hub:
40 = 40 PPR* 450 = 450 PPR* 1200 = 1200 PPR	"no entry" = Voltage output	1 = 5V dc ± 10%	8 = 8mm	"no entry" = Through/No Hub
50 = 50 PPR* 500 = 500 PPR* 1500 = 1500 PPR	C = Open collector output	(line driver output only)	10 = 10mm	F1 = Through/Hub/Set Screw
60 = 60 PPR* 512 = 512 PPR* 1800 = 1800 PPR	E = Line driver output	3 = 5 ~ 12V dc ± 10%		
100 = 100 PPR* 600 = 600 PPR 2000 = 2000 PPR		4 = 24V dc ± 10%		
200 = 200 PPR* 720 = 720 PPR 2048 = 2048 PPR		(open collector output only)		
250 = 250 PPR* 800 = 800 PPR 2500 = 2500 PPR				
300 = 300 PPR* 900 = 900 PPR 3600 = 3600 PPR				
360 = 360 PPR* 1000 = 1000 PPR 4500 = 4500 PPR				
400 = 400 PPR* 1024 = 1024 PPR 9000 = 9000 PPR				

*signifies only resolutions available with F1 Bore/Hub


PART NUMBER: MEH30

DESCRIPTION: incremental encoder

CIRCUIT CONNECTIONS




OUTPUT WAVEFORM



The position of Z phase against A, B phase is not specified

REV.	DESCRIPTION	DATE
A	NEW DRAWING	7/30/2007



TOLERANCE:
±0.3mm UNLESS OTHERWISE
SPECIFIED




CUI INC

20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

TITLE: Incremental Encoder REV: A

PART NO: MEH30 UNITS: MM [INCHES]

DRAWN BY: JMS APPROVED BY: SCALE: 1:1



Cable Color	Red	White	Green	Yellow	Black
Output Type	Power	A-Phase	B-Phase	Z-Phase	0V

COPYRIGHT 2007
BY CUI INC.

PC FILE NAME:
MEH30