

**PART NUMBER:** MES12-2000PST**DESCRIPTION:** incremental encoder**ELECTRICAL SPECIFICATIONS**

output waveform	Square Wave
output signals	A, B, Z phase
current consumption	≤40 mA
frequency response	0~50 KHz X (by multiplication) Voltage Output - 100KHz Open collector
output phase difference	See output waveform
supply voltage	5 V dc ± 10%
output resolution (ppr)	4000, 8000, 16000, 32000
waveform fall / rise time	2μ or less (output cable 1m or less)

MECHANICAL SPECIFICATIONS

max shaft load, radial:	0.98N (100gf)
axial:	0.98N (100gf)
starting torque	1 x 10 ⁻³ N·m, 10 gf·cm
max rotational speed	6000 RPM
shock resistance	500 m/s ² (50G) 3 times each on XYZ
vibration proof	55 Hz, double amplitude 1.5mm, 2 hours each on XYZ
weight	40 g (with 1m cable)
cable	3mm outside diameter 5-core vinyl wire, insulated shield cable (length 1m)

ENVIRONMENTAL SPECIFICATIONS

operating temp	0° to +50° C
storage temp	-20° to +80° C
humidity	RH 35%~90% non collecting

ORDERING INSTRUCTIONS

MES12 - 2000PSTXXX

Resolution (PPR):
 2 = 2000 X 2 (4,000 PPR)
 4 = 2000 X 4 (8,000 PPR)
 8 = 2000 X 8 (16,000 PPR)
 16 = 2000 X 16 (32,000 PPR)


Output:
 "no entry" = TTL voltage output
 C = Open collector output
 E = Line driver output

PART NUMBER: MES12-2000PST


DESCRIPTION: incremental encoder

CIRCUIT CONNECTIONS


Voltage Output




Open Collector Output (C)






Line Driver Output (E)



OUTPUT WAVEFORM



REV.	DESCRIPTION	DATE
A	NEW DRAWING	7/27/2007



TOLERANCE:
±0.3mm UNLESS OTHERWISE
SPECIFIED



CUI INC

20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

TITLE: Incremental Encoder	REV: A
PART NO: MES12	UNITS: MM [INCHES]
DRAWN BY: JMS	APPROVED BY:
	SCALE: 2:1

Cable Color	Red	White	Green	Yellow	Black	-	-	-
Output Type	Power	A-Phase	B-Phase	Z-Phase	0V	-	-	-

COPYRIGHT 2007
BY CUI INC.

PC FILE NAME: MES12