



SERIES: PLDA25 | **DESCRIPTION:** LED DRIVER

FEATURES

- up to 25 W continuous power
- universal input range (90~305 Vac)
- single output
- dimming options: PWM, 1~10 Vdc
- power factor correction ≥ 0.9
- constant current
- low profile for easy installation
- IP67 rated
- over voltage, and continuous short circuit protection
- UL 8750, IEC/EN61347-2-13 approval
- EN61000-3-2 Class C (harmonic current) approval
- efficiency up to 86%
- suitable for LED lighting and signage applications



MODEL	output voltage range ¹		output current	output power max	ripple and noise ²	efficiency
	min (Vdc)	max (Vdc)	(mA)	(W)	max (mVp-p)	typ (%)
PLDA25-530-277	9	48	530	25.44	480	86
PLDA25-700-277	9	36	700	25.2	360	84
PLDA25-1100-277	9	24	1100	26.4	240	86

Notes: 1. constant current region
 2. ripple and noise are measured at 20MHz bandwidth with a 0.1uF ceramic capacitor and 10uF aluminum capacitor.

PART NUMBER KEY

PLDA25 - XXXX - 277XXX

Base Number

Output Current

Input Voltage
 277 = (90~305 Vac)

Dimming
 PE = PWM, 1~10 Vdc
 "blank" = no dimming

IP Rating
 "blank" = IP64
 A = IP67

INPUT

parameter	conditions/description	min	typ	max	units
voltage		90 127		305 420	Vac Vdc
frequency		47		63	Hz
current	at 115 Vac, full load at 230 Vac, full load		0.3 0.14		A A
inrush current	at 240 Vac, cold start, 25°C, after 100 μs			5	A
leakage current	at 277 Vac			0.5	mA
power factor correction	at 115 Vac/230 Vac, 75~100% load at 277 Vac, 100% load	0.9 0.9			
no load power consumption				1	W

OUTPUT

parameter	conditions/description	min	typ	max	units
current line regulation	measured from high line to low line at full load			±5	%
current load regulation	measured from min. to max. of constant current region			±5	%
constant current accuracy	at nominal input and full load			±5	%
switching frequency			60		kHz
start-up time	at 90 Vac			0.5	s
temperature coefficient			±0.05		%/°C

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	TVS clamp				
short circuit protection	hiccup mode, auto recovery				

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output, for 1 minute			3,750	Vac
isolation resistance	input to output	100			MΩ
safety approvals	UL8750, IEC/EN61347-1, IEC/EN61347-2-13, PSE				
EMI/EMC	FCC Part 15 Class B/EN55015, EN61547, EN61000-4-(2,3,4,5,6), EN61000-3-2 Harmonic Class C, EN61000-3-3				
MTBF	as per MIL-HDBK-217F, at 25°C		200,000		hours
RoHS	2011/65/EU				

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature	see derating curves	-40		70	°C
storage temperature		-40		85	°C
operating humidity	non-condensing	20		95	%
operating altitude				3,000	m

MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	5.511 x 1.181 x 0.787 (140 x 30 x 20 mm)				inches
weight			100		g


MECHANICAL DRAWING

MODELS WITHOUT DIMMING

units: inches[mm]
 tolerance: ±0.02[±0.5]
 unless otherwise specified

INPUT WIRE CONNECTIONS	
Color	Function
Black	ACL
White	ACN

OUTPUT WIRE CONNECTIONS	
Color	Function
Red	+Vo
Black	-Vo




MODELS WITH DIMMING




units: inches[mm]
 tolerance: ±0.02[±0.5]
 unless otherwise specified

INPUT WIRE CONNECTIONS	
Color	Function
Black	ACL
White	ACN







OUTPUT WIRE CONNECTIONS	
Color	Function
Red	+Vo
Black	-Vo
Blue	D+
White	D-



DERATING CURVES




EFFICIENCY CURVES



APPLICATION NOTES

1. Dimming

Dimming should be controlled from the dimming controller with PWM or 1~10 Vdc.



1~10 Vdc Dimming

Voltage	1V	2V	3V	4V	5V	6V	7V	8V	9V	10V (open)
Output Current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%

PWM Dimming (@ 1kHz, 10V)

Duty Cycle	10%	20%	30%	40%	50%	60%	70%	80%	90%	100% (open)
Output Current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%

REVISION HISTORY

rev.	description	date
1.0	initial release	09/22/2014

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.