


PART NUMBER: VAD6 series**DESCRIPTION:** dc-dc converter**features**

- 6W isolated output
- efficiency to 82%
- regulated outputs
- Pi input filter
- low ripple and noise
- 24-Pin DIP package
- continuous short circuit protection



model number ^{1, 2, 3}	input voltage	output voltage	output current	input current		efficiency
				no load	full load	
VAD6-D12-S3R3	9-18VDC	3.3VDC	1000mA	7.5mA	393mA	70%
VAD6-D12-S5	9-18VDC	5VDC	1000mA	7.5mA	545mA	76%
VAD6-D12-S12	9-18VDC	12VDC	470mA	7.5mA	585mA	80%
VAD6-D12-S15	9-18VDC	15VDC	400mA	7.5mA	625mA	80%
VAD6-D12-D5	9-18VDC	±5VDC	±500mA	12mA	545mA	76%
VAD6-D12-D12	9-18VDC	±12VDC	±230mA	12mA	575mA	80%
VAD6-D12-D15	9-18VDC	±15VDC	±190mA	12mA	590mA	80%
VAD6-D24-S3R3	18-36VDC	3.3VDC	1000mA	5mA	197mA	70%
VAD6-D24-S5	18-36VDC	5VDC	1000mA	5mA	265mA	78%
VAD6-D24-S12	18-36VDC	12VDC	470mA	5mA	285mA	82%
VAD6-D24-S15	18-36VDC	15VDC	400mA	5mA	305mA	82%
VAD6-D24-D5	18-36VDC	±5VDC	±500mA	7.5mA	265mA	78%
VAD6-D24-D12	18-36VDC	±12VDC	±230mA	7.5mA	285mA	81%
VAD6-D24-D15	18-36VDC	±15VDC	±190mA	7.5mA	295mA	81%
VAD6-D48-S3R3	36-72VDC	3.3VDC	1000mA	2mA	98mA	70%
VAD6-D48-S5	36-72VDC	5VDC	1000mA	2mA	133mA	78%
VAD6-D48-S12	36-72VDC	12VDC	470mA	2mA	145mA	81%
VAD6-D48-S15	36-72VDC	15VDC	400mA	2mA	154mA	81%
VAD6-D48-D5	36-72VDC	±5VDC	±500mA	3mA	133mA	78%
VAD6-D48-D12	36-72VDC	±12VDC	±230mA	3mA	142mA	81%
VAD6-D48-D15	36-72VDC	±15VDC	±190mA	3mA	147mA	81%

NOTES:

1. suffix "HM" for 1.5K Vdc isolation
2. suffix "H" for 3K Vdc isolation
3. suffix "-SMT" for SMT case style

**PART NUMBER:** VAD6 series**DESCRIPTION:** dc-dc converter**INPUT**

input voltage range	12V	9-18V
	24V	18-36
	48V	36-72
input filter		Pi Type

OUTPUT

voltage accuracy		±2.0% max.
voltage balance(dual)		±1.0% max.
temperature coefficient		±0.05% / °C max.
ripple and noise, 20MHz BW	3.3V / 5V	100mV p-p max.
	12V / 15V	1% p-p max.
short circuit protection		continuous
line regulation	single/dual ¹	±0.5%
load regulation	single ²	±0.5%
	dual ³	±1.0%

GENERAL SPECIFICATIONS

efficiency		see table
isolation resistance		10 ⁹ Ohms
switching frequency		100kHz min.
isolation resistance		10 ⁹ Ohms
operating temperature range		-25°C to +71°C
storage temperature		-40°C to +100°C
case temp.(plastic case)		95°C max.
	(copper case)	100°C max.
cooling		free air convection
dimensions		1.25x0.8x0.4 inches
		(31.8x20.3x10.2mm)

ISOLATION VOLTAGE

500 VDC min	standard models
1.5K VDC min	suffix "HM" models
3K VDC min ⁴	suffix "H" models

CASE MATERIAL

standard models	non-conductive black plastic
suffix "HM" models	black coated copper with non-conductive base

NOTES:


1. measured from high line to low line
2. measured from full load to 10% load
3. measured from full load to 1/4 load
4. non-conductive black plastic only

PART NUMBER: VAD6 series


DESCRIPTION: dc-dc converter

DIMENSIONS (mm)

NOTE: Pin Size is 0.02" Inch (0.5mm) DIA
All Dimensions In Inches(mm)
Tolerance Inches: x.xx= ±0.02, x.xxx= ±0.010
Millimeters: x.x= ±0.5, x.xx= ±0.25



DERATING CURVE



PIN CONNECTIONS

Pin	500 VDC				1.5K & 3K VDC				
	Single Output		Dual Output		Single Output		Dual Output		
	DIP	SMD	DIP	SMD	DIP	SMD	DIP	SMD	
1,24	+V Input		+V Input		1,24	NP	NC	NP	NC
2,23	NC		-V Output		2,3	-V Input		-V Input	
3,22	NC		Common		4,5	NP	NC	NP	NC
4	NP	NC	NP	NC	9	NC		Common	
5	NP	NC	NP	NC	10,15	NC		NC	
9	NP	NC	NP	NC	11	NC		-V Output	
10,15	-V Output		Common		12,13	NP	NC	NP	NC
11,14	+V Output		+V Output		14	+V Output		+V Output	
12,13	-V Input		-V Input		16	-V Output		Common	
16	NP	NC	NP	NC	20,21	NP	NC	NP	NC
20,21	NP	NC	NP	NC	22,23	+V Input		+V Input	

*NP-NO PIN

*NC-NO CONNECTION WITH PIN