

SERIES: VQE50W | **DESCRIPTION:** DC-DC CONVERTER

FEATURES


- up to 50 W isolated output
- industry standard quarter brick package
- 4:1 input range (9~36 V, 18~75 V)
- single output from 3.3~48 V
- 1,500 V isolation
- tantalum free capacitors used
- over current, over temperature, over voltage, and short circuit protections
- remote on/off
- very high efficiency up to 92%



| MODEL | input voltage range (Vdc) | output voltage (Vdc) | output current max (A) | output power max (W) | ripple and noise ¹ max (mVp-p) | efficiency typ (%) |
|-----------------|---------------------------|----------------------|------------------------|----------------------|---|--------------------|
| VQE50W-Q24-S3R3 | 9 ~ 36 | 3.3 | 10 | 33 | 100 | 90.5 |
| VQE50W-Q24-S5 | 9 ~ 36 | 5 | 10 | 50 | 100 | 91.5 |
| VQE50W-Q24-S12 | 9 ~ 36 | 12 | 4.16 | 50 | 150 | 91.5 |
| VQE50W-Q24-S15 | 9 ~ 36 | 15 | 3.33 | 50 | 150 | 91.5 |
| VQE50W-Q24-S24 | 9 ~ 36 | 24 | 2.08 | 50 | 240 | 90 |
| VQE50W-Q24-S48 | 9 ~ 36 | 48 | 1.04 | 50 | 480 | 88.5 |
| VQE50W-Q48-S3R3 | 18 ~ 75 | 3.3 | 10 | 33 | 100 | 90 |
| VQE50W-Q48-S5 | 18 ~ 75 | 5 | 10 | 50 | 100 | 92 |
| VQE50W-Q48-S12 | 18 ~ 75 | 12 | 4.16 | 50 | 150 | 92 |
| VQE50W-Q48-S15 | 18 ~ 75 | 15 | 3.33 | 50 | 150 | 91 |
| VQE50W-Q48-S24 | 18 ~ 75 | 24 | 2.08 | 50 | 240 | 90.5 |
| VQE50W-Q48-S48 | 18 ~ 75 | 48 | 1.04 | 50 | 480 | 89 |

Notes: 1. ripple and noise are measured at 20 MHz BW with 10µF tantalum capacitor and 1µF ceramic capacitor across output

PART NUMBER KEY



INPUT

| parameter | conditions/description | min | typ | max | units |
|---|---|------------|-----|-----|-------|
| operating input voltage | 24 V input | 9 | 24 | 36 | Vdc |
| | 48 V input | 18 | 48 | 75 | Vdc |
| surge voltage | 100 ms max. 24 V input 48 V input | | | 500 | Vdc |
| | | | | 100 | Vdc |
| under voltage lockout | power up | 24 V input | 8.8 | | Vdc |
| | | 48 V input | 17 | | Vdc |
| | power down | 24 V input | 8 | | Vdc |
| | | 48 V input | 16 | | Vdc |
| positive logic remote on/off ¹ | | | | | |
| filter | PI type | | | | |

- Notes:
- logic compatibility, open collector ref to -input
Module ON, 3.5 ~ 75 Vdc or open circuit
Module OFF, <1.2 Vdc
 - negative logic remote on/off available
Module ON, <1.2 Vdc current limit, 110~165% nominal output
Module OFF, 3.5 ~ 75 Vdc or open circuit

OUTPUT

| parameter | conditions/description | min | typ | max | units |
|--------------------------|--------------------------------------|-----|-------|------|-------|
| line regulation | measured from high line to low line | | | ±0.2 | % |
| load regulation | measured from full load to zero load | | | ±0.2 | % |
| voltage accuracy | | | | ±1.5 | % |
| transient response | 25% step load change | | | 500 | µs |
| external trim adj. range | | | ±10 | | % |
| switching frequency | 100% load, input voltage range | | 300 | | kHz |
| temperature coefficient | | | ±0.03 | | %/°C |

PROTECTIONS

| parameter | conditions/description | min | typ | max | units |
|-----------------------------|--------------------------|-----|-----|-----|-------|
| over voltage protection | %Vo | 115 | | 140 | % |
| short circuit protection | continuous | | | | |
| current limit | % nominal output current | 110 | | 165 | % |
| thermal shutdown case temp. | | | 110 | | °C |


SAFETY AND COMPLIANCE

| parameter | conditions/description | min | typ | max | units |
|-----------------------|-----------------------------------|-------|-------|-----|-------|
| isolation voltage | input to output | 1,500 | | | Vdc |
| | input to case | 1,500 | | | Vdc |
| | output to case | 1,500 | | | Vdc |
| isolation resistance | | 10 | | | MΩ |
| isolation capacitance | | | 1,000 | | pF |
| safety approvals | UL 60950-1, CE | | | | |
| RoHS compliant | yes | | | | |
| MTBF | MIL-STD-217F, GB, 25°C, full load | | TBD | | hours |

ENVIRONMENTAL

| parameter | conditions/description | min | typ | max | units |
|----------------------------|------------------------|-----|-----|-----|-------|
| case operating temperature | | -40 | | 105 | °C |
| storage temperature | | -55 | | 125 | °C |
| humidity | non-condensing | | | 95 | % |

DERATING CURVE




MECHANICAL

| parameter | conditions/description | min | typ | max | units |
|---------------|--|-----|-----|-----|-------|
| dimensions | 1.45 x 2.28 x 0.50 (36.8 x 57.9 x 12.7 mm) | | | | inch |
| case material | aluminum | | | | |
| weight | | | 63 | | g |

MECHANICAL DRAWING

units: inches[mm]
 tolerance:
 inches: X.XX = ±0.02
 X.XXX = ±0.010
 mm: X.XX = ±0.5
 X.XXX = ±0.25



| PIN CONNECTIONS | |
|-----------------|----------|
| PIN | FUNCTION |
| 1 | +Vin |
| 2 | On/Off |
| 3 | -Vin |
| 4 | -Vo |
| 5 | -S |
| 6 | TRIM |
| 7 | +S |
| 8 | +Vo |

Note: All specifications measured at 25°C, nominal input voltage, and full load unless otherwise noted.

REVISION HISTORY

| rev. | description | date |
|------|--|------------|
| 1.0 | initial release | 08/22/2012 |
| 1.01 | added negative logic option to part number key, updated derating curve | 03/04/2013 |
| 1.02 | updated spec | 03/18/2013 |

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.