


SERIES: VDRS-100 | DESCRIPTION: AC-DC DIN RAIL
FEATURES

- up to 96 W continuous power
- DIN Rail power supplies
- universal input (88~264 Vac / 124~370 Vdc)
- single output from 12~48 Vdc
- over voltage, over load, over temperature, and short circuit protections
- UL 1310, UL 508, and TUV safety approvals
- long life electrolytic capacitors
- efficiency up to 88%



| MODEL | output voltage (Vdc) | output current max (A) | output power max (W) | ripple and noise ¹ max (mVp-p) | efficiency (%) |
|-------------|-------------------------|---------------------------|-------------------------|---|-------------------|
| VDRS-100-12 | 12 | 7.5 | 90 | 180 | 87 |
| VDRS-100-15 | 15 | 6.4 | 96 | 180 | 87 |
| VDRS-100-24 | 24 | 4 | 96 | 180 | 88 |
| VDRS-100-48 | 48 | 2 | 96 | 250 | 87 |

Note: 1. At full load, 230 Vac input, measured at 20MHz bandwidth with a 47 μ F and 0.1 μ F parallel capacitors on the output.
2. All specifications are measured at Ta=25°C, 230 Vac input voltage, and rated output load unless otherwise specified.

PART NUMBER KEY


INPUT

| parameter | conditions/description | min | typ | max | units |
|----------------|------------------------|------|-----|------|-------|
| voltage | | 88 | | 264 | Vac |
| | | 124 | | 370 | Vdc |
| frequency | | 47 | | 63 | Hz |
| current | 115 Vac | | | 1.1 | A |
| | 230 Vac | | | 0.55 | A |
| inrush current | 115 Vac, cold start | | | 30 | A |
| | 230 Vac | | | 60 | A |
| power factor | at 115 Vac, full load | 0.98 | | | |
| | at 230 Vac, full load | 0.92 | | | |

OUTPUT

| parameter | conditions/description | min | typ | max | units |
|-------------------------|-----------------------------------|-----|-------|-----|-------|
| line regulation | | | | ±1 | % |
| load regulation | | | | ±2 | % |
| temperature coefficient | (0 ~ 50°C) | | ±0.03 | | %/°C |
| hold-up time | at 115 Vac, cold start | 16 | | | ms |
| | at 230 Vac, cold start | 32 | | | ms |
| adjustability | adjustable with built-in trim pot | | | ±10 | % |

PROTECTIONS

| parameter | conditions/description | min | typ | max | units |
|--------------------------|--|-----|-----|-----|-------|
| over voltage protection | latch-off mode | 115 | | 150 | % |
| over load protection | constant current limiting, automatically recovers after fault condition is removed | 102 | | | % |
| short circuit protection | output shut down and auto restart | | | | |

SAFETY & COMPLIANCE

| parameter | conditions/description | min | typ | max | units |
|----------------------|--|-----|-----|-------|-------|
| isolation voltage | input to output for 1 minute | | | 3,000 | Vac |
| | input to case for 1 minute | | | 1,500 | Vac |
| isolation resistance | input to output, input to case, output to case, 500 Vdc | 100 | | | MΩ |
| safety approvals | UL 508, TUV EN 60950-1, UL 1310 ¹ NEC class 2 compliant | | | | |
| EMI/EMC ² | EN 55022 : 2006(Class B), EN 61204-3: 2000, EN 61000-6-3: 2007, EN 61000-3-2,3 :2006, EN 55024, EN 61204-3: 2000, EN 61000-6-1: 2007 (EN 61000-4-2,3,4,5,6,8,11) | | | | |
| leakage current | at 230 Vac | | | 1 | mA |
| RoHS | 2011/65/EU | | | | |

Note: 1. UL 1310 only for 24 & 48 Vdc output models.
2. The power supply is considered a component which will be installed into final equipment. The final equipment still must be tested to meet the necessary EMC directives.



ENVIRONMENTAL

| parameter | conditions/description | min | typ | max | units |
|-----------------------|---|-----|-----|-----|-------|
| operating temperature | see derating curves | -20 | | 70 | °C |
| storage temperature | | -40 | | 85 | °C |
| operating humidity | non-condensing | 20 | | 90 | % |
| storage humidity | | 10 | | 95 | % |
| vibration | (10 ~ 500 Hz, 1 hour per axis, 3 hours total) | | 5 | | Grms |

MECHANICAL DRAWING


units: mm

use with TS35/7.5 or TS35/15 rails




DERATING CURVES

Output Power vs. Ambient Temperature



Output Power vs. Input Voltage (at 25°C)



ACTIVE DC SIGNAL - RELAY CONTACT

| | |
|-----------------------|---|
| Contact Close | When the output voltage reaches the adjusted output voltage |
| Contact Open | When the output voltage drops below 90% |
| Contact Ratings (MAX) | 30 V / 1 A resistive load |

REVISION HISTORY

| rev. | description | date |
|------|--|------------|
| 1.0 | initial release | 06/03/2010 |
| 1.01 | new template applied | 08/18/2011 |
| 1.02 | V-Infinity branding removed, drawing updated | 08/23/2012 |
| 1.03 | updated datasheet | 01/10/2017 |

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.