



## Declaration of Conformity

Manufacturer:  
**CUI Inc**  
20050 SW 112th Ave  
Tualatin, OR 97062

For the following equipment:

AC-DC Internal Power Supply  
**CUI Series: VOF-260B**  
Models: See next page,

This declaration of conformity is issued under the sole responsibility of the manufacturer.  
The object of the declaration described above is in conformity with the relevant Union harmonization legislations and their amendments:

**Low Voltage Directive 2014/35/EU**  
**EMC Directive 2014/30/EU**  
**RoHS Directive 2011/65/EU and (EU) 2015/863**

References to the relevant harmonized standards used, including the date of the standard, or references to the other technical specifications, including the date of the specification, in relation to which conformity is declared:

<b>Health &amp; Safety</b>	EN IEC 62368-1:2020+A11:2020 IEC 62368-1:2018
<b>EMC</b>	EN 55032:2015+A11:2020; EN 55035:2017+A11:2020 EN IEC 61000-3-2:2019+A1:2021; EN 61000-3-3:2013+A1:2019
<b>RoHS</b>	EN IEC 63000:2018

Note: These component level power supplies are intended exclusively for inclusion within other equipment. Protection against electric shock and Electromagnetic Compatibility (EMC) must be checked when the equipment is built-in a completed product or forms a part of a complete system.

An additional delta evaluation of the above-listed equipment concerning the differences between the requirements of the harmonized standard EN 62368-1:2014 (with all applicable corrections) and EN IEC 62368-1:2020, and IEC 62368-1:2018 has been performed and concludes that the safety objectives of the low-voltage targets (2014/35/EU) are met.



(manufacturer)

Link Lu  
Product Compliance Specialist

**Shenzhen, China**

(place)

**08/28/2023**

(date)



(manufacturer)

Editha Vergara  
Global Director, Safety, Environmental

**Tualatin, Oregon, USA**

(place)

**08/28/2023**

(date)

## MODEL LIST

VOF-260B-XX (where XX = 12, 24, 36, 48 denote output voltage)

Model	Input voltage (Vac)	Frequency (Hz)	Input current (A)	Output voltage (Vdc)
VOF-260B-12	100-240	47-63	3.5-1.2	Main: 12
				Fan: 12
VOF-260B-24	100-240	47-63	3.5-1.2	Main: 24
				Fan: 12
VOF-260B-36	100-240	47-63	3.5-1.2	Main: 36
				Fan: 12
VOF-260B-48	100-240	47-63	3.5-1.2	Main: 48
				Fan: 12

VOF-260B-XX-BP (where XX = 12, 24, 36, 48 denote output voltage)

Model	Input voltage (Vac)	Frequency (Hz)	Input current (A)	Output voltage (Vdc)
VOF-260B-12-BP	100-240	47-63	3.5-1.2	Main: 12
				Fan: 12
VOF-260B-24-BP	100-240	47-63	3.5-1.2	Main: 24
				Fan: 12
VOF-260B-36-BP	100-240	47-63	3.5-1.2	Main: 36
				Fan: 12
VOF-260B-48-BP	100-240	47-63	3.5-1.2	Main: 48
				Fan: 12

VOF-260B-XX-C (where XX = 12, 24, 36, 48 denote output voltage)

Model	Input voltage (Vac)	Frequency (Hz)	Input current (A)	Output voltage (Vdc)
VOF-260B-12-C	100-240	47-63	3.5-1.2	Main: 12
				Fan: 12
VOF-260B-24-C	100-240	47-63	3.5-1.2	Main: 24
				Fan: 12
VOF-260B-36-C	100-240	47-63	3.5-1.2	Main: 36
				Fan: 12
VOF-260B-48-C	100-240	47-63	3.5-1.2	Main: 48
				Fan: 12

## REVISION HISTORY

---

<b>rev.</b>	<b>description</b>	<b>date</b>
1.0	initial release	05/22/23
1.01	Add model name	08/28/23

The revision history provided is for informational purposes only and is believed to be accurate.