



SERIES: ACZ12

DESCRIPTION: mechanical incremental encoder

ELECTRICAL SPECIFICATIONS

parameter	conditions/description
output waveform	square wave
output signals	A, B phase
current consumption	10 mA
output phase difference	T1, T2, T3, T4 ≥ 3.5 ms @ 60 rpm (see output waveform)
supply voltage	12 V dc max.
output resolution	12, 24 ppr
switch rating	12 V dc, 50 mA (ACZ12BRXE models only)
insulation resistance	300 V dc, 100 MΩ
withstand voltage	300 V ac


MECHANICAL SPECIFICATIONS

parameter	conditions/description	min	nom	max	units
shaft load	axial			3	kgf
rotational torque	with detent click	30		200	gf · cm
	without detent click	60	80	100	gf · cm
push switch operational force	(ACZ12BRXE models only)	300		900	gf · cm
push switch life	(ACZ12BRXE models only)			50,000	
rotational life				30,000	cycles

ENVIRONMENTAL SPECIFICATIONS

parameter	conditions/description	min	nom	max	units
operating temperature		-10		75	°C
storage temperature		-20		85	°C
humidity		85			% RH
vibration	0.75 mm max. travel for 2 hours	10		55	Hz


PART NUMBER KEY




SERIES: ACZ12

DESCRIPTION: mechanical incremental encoder


SHAFT OPTIONS



OUTPUT WAVEFORM




DETENT POSITIONS




SLIDING NOISE

t = Masking time to avoid chatter (5mS) $V_1 = V_2 = 1V$ max.




SUGGESTED FILTER



SERIES: ACZ12


DESCRIPTION: mechanical incremental encoder

MECHANICAL DRAWING (horizontal)



MECHANICAL DRAWING (vertical)

ACZ12NBRXE



ACZ12BRXE

