



SERIES: ACZ11

DESCRIPTION: mechanical incremental encoder

ELECTRICAL SPECIFICATIONS

parameter	conditions/description
output waveform	square wave
output signals	A, B phase
current consumption	10 mA
output phase difference	T1, T2, T3, T4 \geq 3.5 ms @ 60 rpm (see output waveform)
supply voltage	5 V dc max.
output resolution	12, 15, 20, 30 ppr
switch rating	12 V dc, 50 mA (ACZ11BRXE models only)
insulation resistance	300 V dc, 100 M Ω
withstand voltage	300 V ac


MECHANICAL SPECIFICATIONS

parameter	conditions/description	min	nom	max	units
shaft load	axial			8	kgf
rotational torque	with detent click	60	140	220	gf · cm
	without detent click	60	80	100	gf · cm
push switch operational force	(ACZ11BRXE models only)	300		900	gf · cm
push switch life	(ACZ11BRXE models only)			50,000	cycles
rotational life				30,000	cycles

ENVIRONMENTAL SPECIFICATIONS

parameter	conditions/description	min	nom	max	units
operating temperature		-10		65	$^{\circ}$ C
storage temperature		-40		75	$^{\circ}$ C
humidity		85			% RH
vibration	0.75 mm max. travel for 2 hours	10		55	Hz


PART NUMBER KEY



SERIES: ACZ11

DESCRIPTION: mechanical incremental encoder

SHAFT OPTIONS



BUSHING		
Condition	H	
1	M7-P0.75	5
2	M7-P0.75	7
4	smooth	5
5	smooth	7

switch travel for ACZ11BRXE only

H=5

	15KQ	20KQ	25KQ
L	15	20	25
I	7	10	12

H=5

	15S	20S	25S
L	15	20	25

H=5

	15F	20F	25F
L	15	20	25
F	8	12	12

H=7

	15KQ	20KQ	25KQ
L	15	20	25
I	5	8.5	10


H=7

	15S	20S	25S
L	15	20	25

H=7

	15F	20F	25F
L	15	20	25
F	8	12	12


OUTPUT WAVEFORM



CW direction (@ 60 rpm)


DETENT POSITIONS

Model 12C & 20C



CW direction →


Model 15P30C



CW direction →


SLIDING NOISE

t = Masking time to avoid chatter (5mS) $V_1 = V_2 = 1V$ max.



Tested at 60 rpm

SUGGESTED FILTER





R1, R2, R3, R4 = 10kΩ
C1, C2 = 0.01μF

SERIES: ACZ11


DESCRIPTION: mechanical incremental encoder

MECHANICAL DRAWING (horizontal)


ACZ11NBRXE





PANEL CUT-OUT




PCB LAYOUT




ACZ11BRXE



PANEL CUT-OUT





PCB LAYOUT




MECHANICAL DRAWING (vertical)


ACZ11NBRXE





PANEL CUT-OUT




PCB LAYOUT



ACZ11BRXE



PANEL CUT-OUT



PCB LAYOUT

