


SERIES: PDME2-D | **DESCRIPTION:** DC-DC CONVERTER**FEATURES**

- 2 W isolated output
- single/dual unregulated outputs
- 1500 Vdc isolation
- continuous short circuit protection
- extended temperature range (-40~105°C)
- no-load input current as low as 8mA
- efficiency up to 88%
- designed to meet UL/EN/BS EN 62368

**MODEL**

MODEL	input voltage		output voltage	output current		output power	ripple & noise ¹	efficiency ²
	typ (Vdc)	range (Vdc)		min (mA)	max (mA)	max (W)	max (mVp-p)	typ (%)
PDME2-3-S3-D	3.3	2.97~3.63	3.3	40	400	1.3	200	78
PDME2-3-S5-D	3.3	2.97~3.63	5	40	400	2	200	78
PDME2-5-D3-D	5	4.5~5.5	±3.3	±30	±303	2	200	78
PDME2-5-D5-D	5	4.5~5.5	±5	±20	±200	2	200	84
PDME2-5-D7-D	5	4.5~5.5	±7	±14	±143	2	200	84
PDME2-5-D9-D	5	4.5~5.5	±9	±11	±111	2	200	85
PDME2-5-D12-D	5	4.5~5.5	±12	±8	±83	2	200	85
PDME2-5-D15-D	5	4.5~5.5	±15	±7	±67	2	200	86
PDME2-5-D24-D	5	4.5~5.5	±24	±4	±42	2	200	86
PDME2-5-S3-D	5	4.5~5.5	3.3	40	400	2	200	78
PDME2-5-S5-D	5	4.5~5.5	5	40	400	2	200	84
PDME2-5-S9-D	5	4.5~5.5	9	22	222	2	200	85
PDME2-5-S12-D	5	4.5~5.5	12	17	167	2	200	85
PDME2-5-S15-D	5	4.5~5.5	15	13	133	2	200	86
PDME2-5-S24-D	5	4.5~5.5	24	8	83	2	200	86
PDME2-12-D5-D	12	10.8~13.2	±5	±20	±200	2	180	80
PDME2-12-D9-D	12	10.8~13.2	±9	±11	±111	2	180	82
PDME2-12-D12-D	12	10.8~13.2	±12	±8	±83	2	180	83
PDME2-12-D15-D	12	10.8~13.2	±15	±7	±67	2	180	83
PDME2-12-D24-D	12	10.8~13.2	±24	±4	±42	2	200	85
PDME2-12-S5-D	12	10.8~13.2	5	40	400	2	180	82
PDME2-12-S9-D	12	10.8~13.2	9	23	222	2	180	82
PDME2-12-S12-D	12	10.8~13.2	12	17	167	2	180	84
PDME2-12-S15-D	12	10.8~13.2	15	13	133	2	180	85
PDME2-12-S24-D	12	10.8~13.2	24	8	83	2	200	86
PDME2-15-D15-D	15	13.5~16.5	±15	±7	±67	2	180	81
PDME2-15-S5-D	15	13.5~16.5	5	40	400	2	180	79


MODEL (CONTINUED)

	input voltage		output voltage	output current		output power	ripple & noise ¹	efficiency ²
	typ (Vdc)	range (Vdc)		min (mA)	max (mA)		max (mVp-p)	
PDME2-15-S9-D	15	13.5~16.5	9	23	222	2	180	82
PDME2-15-S15-D	15	13.5~16.5	15	13	133	2	180	79
PDME2-24-D5-D	24	21.6~26.4	±5	±20	±200	2	180	80
PDME2-24-D9-D	24	21.6~26.4	±9	±11	±111	2	180	81
PDME2-24-D12-D	24	21.6~26.4	±12	±8	±83	2	180	83
PDME2-24-D15-D	24	21.6~26.4	±15	±7	±67	2	180	83
PDME2-24-D24-D	24	21.6~26.4	±24	±4	±42	2	200	83
PDME2-24-S5-D	24	21.6~26.4	5	40	400	2	180	82
PDME2-24-S9-D	24	21.6~26.4	9	23	222	2	180	82
PDME2-24-S12-D	24	21.6~26.4	12	17	167	2	180	86
PDME2-24-S15-D	24	21.6~26.4	15	13	133	2	180	88
PDME2-24-S24-D	24	21.6~26.4	24	8	83	2	200	88

Notes:

1. Measured at nominal input, 20 MHz bandwidth oscilloscope.
2. Measured at nominal input voltage, full load.
3. All specifications are measured at Ta=25°C, humidity < 75%, nominal input voltage, and rated output load unless otherwise specified.

PART NUMBER KEY



INPUT

parameter	conditions/description		min	typ	max	units
operating input voltage	3.3 Vdc input models		2.97	3.3	3.63	Vdc
	5 Vdc input models		4.5	5	5.5	Vdc
	12 Vdc input models		10.8	12	13.2	Vdc
	15 Vdc input models		13.5	15	16.5	Vdc
	24 Vdc input models		21.6	24	26.4	Vdc
surge voltage	for maximum of 1 second					
	3.3 Vdc input models		-0.7		5	Vdc
	5 Vdc input models		-0.7		9	Vdc
	12 Vdc input models		-0.7		18	Vdc
	15 Vdc input models		-0.7		21	Vdc
	24 Vdc input models		-0.7		30	Vdc
current (full load/no load)	3.3 Vdc input models	3.3 Vdc output		513/12	541/-	mA
		5 Vdc output		778/12	820/-	mA
	5 Vdc input models	3.3 Vdc output		513/8	541/-	mA
		5 & 7 Vdc output		477/8	500/-	mA
		9 & 12 Vdc output		471/8	494/-	mA
		15 & 24 Vdc output		466/8	488/-	mA
	12 Vdc input models			209/8	220/-	mA
	15 Vdc input models			169/8	178/-	mA
	24 Vdc input models			105/8	113/-	mA
filter	filter capacitor					

OUTPUT

parameter	conditions/description		min	typ	max	units
maximum capacitive load ⁴	3.3 Vdc input model	3.3, 5 Vdc output models			2,400	μF
		3.3, 5 Vdc output models			2,400	μF
	5 Vdc input model	±3.3, ±5 Vdc output models			1,200	μF
		9 Vdc output models			1,000	μF
		12, 15 Vdc output models			560	μF
		24, ±12, ±15 Vdc output models			220	μF
		±7, ±9 Vdc output models			470	μF
		±24 Vdc output models			100	μF
	12, 15, 24 Vdc input model	5 Vdc output models			2,400	μF
		±5 Vdc output models			1,200	μF
		9 Vdc output models			1,000	μF
		12, 15 Vdc output models			560	μF
		±9 Vdc output models			500	μF
		±12, ±15 Vdc output models			280	μF
		24 Vdc output models			220	μF
line regulation ⁵	3.3, 5 Vdc input model	3.3 Vdc output models			±1.5	%
		all other output models			±1.2	%
	12, 15, 24 Vdc input model				±1.2	%
load regulation ⁶	3.3 Vdc input model	3.3 Vdc output models		15	20	%
		5 Vdc output models		20	25	%
	5 Vdc input model	3.3 Vdc output models		12	20	%
		5, 7 Vdc output models		9	15	%
		9, 12, 15 Vdc output models		7	10	%
		24 Vdc output models		5	10	%
	12, 15, 24 Vdc input model	5 Vdc output models		7	15	%
		9 Vdc output models		5	10	%
		12 Vdc output models		5	10	%
		15 Vdc output models		4	10	%
		24 Vdc output models		3	10	%

OUTPUT

parameter	conditions/description	min	typ	max	units
switching frequency	100% load, nominal input voltage		220		kHz
	3.3, 5 Vdc input models		260		kHz
	all other input models				
temperature coefficient	at full load		±0.02		%/°C

Note: 4. The specified maximum capacitive load for positive and negative output is identical.
5. For Vin change of 1%.
6. From 10% to full load.

PROTECTIONS

parameter	conditions/description	min	typ	max	units
short circuit protection	continuous, auto recovery				

SAFETY AND COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output for 1 minute at 1 mA	1,500			Vdc
isolation resistance	input to output at 500 Vdc	1,000			MΩ
isolation capacitance	input to output, 100 kHz / 0.1 V		20		pF
conducted emissions	CISPR32/EN55032 CLASS B (see recommended circuit)				
radiated emissions	CISPR32/EN55032 CLASS B (see recommended circuit)				
ESD	IEC/EN61000-4-2 Air ±8kV, Contact ±6kV perf. Criteria B				
radiated immunity	CISPR32/EN55032 CLASS B				
MTBF	as per MIL-HDBK-217F, 25°C	3,500,000			hours
RoHS	yes				

ENVIRONMENTAL


parameter	conditions/description	min	typ	max	units
operating temperature	see derating curves	-40		105	°C
storage temperature		-55		125	°C
storage humidity	non-condensing	5		95	%
case temperature rise	at 25°C		25		°C
vibration	10-150Hz, 5G, 0.75mm. along X, Y and Z				

SOLDERING


parameter	conditions/description	min	typ	max	units
pin soldering resistance	soldering spot is 1.5mm away from case for 10 seconds			300	°C

DERATING CURVES

TEMPERATURE DERATING CURVE
3.3 & 5 Vdc input models




TEMPERATURE DERATING CURVE
12, 15 & 24 Vdc input models




DERATING CURVES (CONTINUED)


OUTPUT REGULATION CURVE
3.3 & 5 Vdc input / 3.3 Vdc output
(nominal input)




OUTPUT REGULATION CURVE
3.3 input / 5 Vdc output
(nominal input)




OUTPUT REGULATION CURVE
5 Vdc input / all other outputs
(nominal input)



OUTPUT REGULATION CURVE
12, 15, 24 Vdc input / 5 Vdc output
(nominal input)




OUTPUT REGULATION CURVE
12, 15, 24 Vdc input / all other outputs
(nominal input)




EFFICIENCY CURVES


EFFICIENCY VS INPUT VOLTAGE
(full load)
PDME2-3-S5-D




EFFICIENCY VS OUTPUT LOAD
($V_{in} = 3.3\text{ V}$)
PDME2-3-S5-D




EFFICIENCY VS INPUT VOLTAGE
(full load)
PDME2-5-D5-D




EFFICIENCY VS OUTPUT LOAD
($V_{in} = 5\text{ V}$)
PDME2-5-D5-D



EFFICIENCY VS INPUT VOLTAGE
(full load)
PDME2-12-S5-D




EFFICIENCY VS OUTPUT LOAD
($V_{in} = 12\text{ V}$)
PDME2-12-S5-D




EFFICIENCY CURVES (CONTINUED)

EFFICIENCY VS INPUT VOLTAGE
(full load)
PDME2-12-S5-D



EFFICIENCY VS OUTPUT LOAD
(Vin = 12 V)
PDME2-12-S5-D



MECHANICAL


parameter	conditions/description	min	typ	max	units
dimensions	20.32 x 10.16 x 8.20 [0.800 x 0.400 x 0.323 inch]				mm
case material	black flame-retardant and heat-resistant plastic (UL94V-0)				
weight			2.4		g

MECHANICAL DRAWING


units: mm [inch]

tolerance: ± 0.25 [± 0.010]pin section tolerance: ± 0.10 [± 0.004]


PIN CONNECTIONS		
PIN	Function Single output	Function Dual output
1	GND	GND
7	NC	NC
8	0V	0V
9	+Vo	+Vo
11	no pin	-Vo
14	Vin	Vin



Dual



Single



Note: Grid 2.54*2.54mm

APPLICATION CIRCUIT

Input and/or output ripple can be further reduced, by connecting a filter capacitor from the input and/or output terminals to ground as shown in Fig 1 & 2. Choosing suitable filter capacitor values is very important for a smooth operation of the modules, particularly to avoid start-up problems caused by capacitor values that are too high. For recommended input and output capacitor values refer to Table 1 & 2.

Figure 1
Single Output Models




Table 1

Vin (Vdc)	Cin (μF / V)	Vo (Vdc)	Co (μF / V)
3.3	10 / 16	3.3	10 / 16
--	--	5	10 / 16
5	4.7 / 16	3.3	10 / 16
--	--	5	10 / 16
--	--	9	2.2 / 16
--	--	12	2.2 / 25
		15	2.2 / 25
--	--	24	1 / 50
12	2.2 / 25	5	10 / 16
15	2.2 / 25	9	2.2 / 25
24	1 / 50	12	2.2 / 25
--	--	15	2.2 / 25
--	--	24	1 / 50

Figure 2
Dual Output Models




Table 2

Vin (Vdc)	Cin (μF / V)	Vo (Vdc)	Co ⁶ (μF / V)
5	4.7 / 16	±3.3	4.7 / 16
--	--	±5	4.7 / 16
		±7	4.7 / 16
--	--	±9	1 / 16
--	--	±12	1 / 25
--	--	±15	1 / 25
--	--	±24	0.47 / 50
12	2.2 / 25	±5	4.7 / 16
15	2.2 / 25	±9	4.7 / 16
24	1 / 50	±12	1 / 25
--	--	±15	1 / 25
--	--	±24	0.47 / 50

Note: 7. The capacitor value of the positive and the negative output is identical.

EMC RECOMMENDED CIRCUIT

Figure 3
Single Output Models




Figure 4
Dual Output Models




Table 3

Recommended External Circuit Components			
Vin (Vdc)	3.3	5	12, 15, 24
C1 / C2	4.7 μ F / 16 V	4.7 μ F / 16 V	4.7 μ F / 50 V
CY	270 pF / 2 kV	270 pF / 2 kV	270 pF / 2 kV
C3 / C4	refer to the Co in Tables 1, 2		
LDM	6.8 μ H	6.8 μ H	6.8 μ H

REVISION HISTORY

rev.	description	date
1.0	initial release	09/05/2023

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC
a bel group

Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.