

SPECIFICATIONS

ELECTRICAL

1. Voltage Rating: 10 VDC
2. Current Rating: 1.0 mA (2.5 mA max)
3. Resolution: 20PPR
4. Insulation Resistance: 500 VDC, 100M
5. Contact Resistance: 1Ω max.


MECHANICAL

1. Detent Positions: 20
2. Rotational Torque: 30-200 gf•cm
3. Axial Load: 10kgf
4. Rotational Life: 100,000 cycles

ENVIRONMENTAL


1. Operating Temp: -10° to +60° C
2. Storage Temp: -40° to +75° C
3. Humidity: 85% RH
4. Vibration: 10 - 55 Hz, 0.75 mm, 2 hrs

OUTPUT WAVEFORM



Sliding Noise

$t = 5mS =$ Masking time to avoid chatter
 $V_1 = V_2 = 2V$ max.



ORDERING INSTRUCTIONS

EC09P20H-XXX

Insert suffix to specify shaft type

		CUI Inc. 20050 SW 112th Ave. Tualatin, OR 97062 Tel: 503/612-2300 FAX: 503/612-2383	
		DRAWN BY JRH	UPDATED 01/23/08
PART NO. EC09P20H-XXX			REV. A