





Specifications

| | | | | | |
|----|--------------------|--|------------------------|-------------|----------|
| 1 | Part No. | GF1205B | | | |
| 2 | Nominal Size | 120 mm. | 5" inch | | |
| 3 | Impedance | $4\ \Omega \pm 15\%$ | at 500 Hz. | 1 V. | |
| 4 | Resonance | 100 Hz. \pm 20 Hz. | FO Hz. | 1 V. | |
| 5 | S.P. Level | 93 dB/w \pm 2 dB | 1 w. 50 cm. average at | | |
| 6 | Response | fo Hz. \sim 20K Hz. MAX 10dB | 300, 400, 500, 600 Hz. | | |
| 7 | Crossover Freq. | Hz. | Hz. | dB/OCT | Net work |
| 8 | Input Power | Nominal Input 10 w. | Handling Capacity | 15 w. | |
| 9 | Operation | Must be normal at program source 10 w. | | | |
| 10 | Buzz, Rattle, etc. | Must be normal at sine wave 4.9 v. | | | |
| 11 | Flux Density | Gauss \pm 10% | | | |
| 12 | Total Flux | Max well min | | | |
| 13 | Magnet | Size 70 x 32 x 10 mm | gr | oz | |
| 14 | Total Weight | gr oz | | | |
| 15 | Load Test | After test meet item 9 and 10 | White noise | 10 W. | 48 Hours |
| 16 | Distortion | % MAX Hz W. | | | |
| 17 | Heat Test | After test meet item 9 and 10 | 70 \pm 2 \pm °C | 20-50 %R.H. | 48 Hours |
| 18 | Humidity Test | After test meet item 9 and 10 | 40 \pm 2 \pm °C | 90-95 %R.H. | 48 Hours |

| | | | |
|-----------|---------|----------|--------|
| PART NO. | GF1205B | UNITS: | mm |
| DRAWN BY: | | PAGE NO: | 1 of 2 |



9615 SW Allen, Suite 103
 Beaverton, OR 97005
 Phone: (503) 643-4899
 800-275-4899
 Fax: (503) 372-1266
 Website: www.cui.com

TITLE:

PART NO.

GF1205B

UNITS:

mm

DRAWN BY:

Page No.

2 of 2