

Material: 30% PBT

MODEL	Ød1	Ød2	ØD	L	P	B1	B2	M	Torque	Mass	mom. inertia
GJ 1.5-1.5	1.5	1.5	9	11.4	8.2	3.2	3.2	2	1.83	0.89	0.092
GJ 1.5-2	1.5	2	9	11.4	8.2	3.2	3.2	2	1.83	0.89	0.092
GJ 1.5-2.5	1.5	2.5	10	11.8	8.4	3.2	3.2	2	2.24	1.08	0.142
GJ 1.5-3	1.5	3	10	11.8	8.4	3.6	3.6	2	2.24	1.08	0.142
GJ 2-3	2	3	10	11.8	8.4	3.6	3.6	2	2.24	1.08	0.142
GJ 2-2	2	2	9	13.2	10	3.2	3.2	2	1.83	0.95	0.102
GJ 3-3	3	3	12	20	14.8	5.1	5.1	3	4.07	2.5	0.449
GJ 4-4	4	4	13	21	15.6	5.2	5.2	3	6.62	3.1	0.704
GJ 4-5	4	5	13	21	15.6	5.2	5.2	3	6.62	3.1	0.704
GJ 5-5	5	5	14	20.8	15.4	5.2	5.2	3	7.13	3.3	0.918
GJ 5-6	5	6	14	20.8	15.4	5.2	5.2	3	7.13	3.3	0.918
GJ 6-6	6	6	15	21.6	16	5.2	5.2	3	8.15	3.9	1.224
GJ 8-8	8	8	19	23.6	16.6	6.8	6.8	4	15.3	7.3	3.977
GJ 10-10	10	10	22	25.6	18.4	7.1	7.1	4	20.4	9.8	7.138
GJK 9.53	9.53	9.53	25	31.6	24	7.3	7.3	4	30.6	14.8	13.25
GJK 10-10	10	10	25	31.6	24	7.3	7.3	4	30.6	14.8	13.25
GJK 12-12	12	12	28	33.9	26.1	7.5	7.5	4	35.7	18.5	21.41





kgfcm g gcm<sup>2</sup>

MODEL	max. angle error	max. end play	max. mis-align	MODEL	max. angle error	max. end play	max. mis-align
GJ 1.5-1.5	3°	±0.3	0.2	GJ 4-5	6°	±0.4	0.4
GJ 1.5-2	3°	±0.3	0.2	GJ 5-5	6°	±0.4	0.4
GJ 1.5-2.5	3°	±0.3	0.2	GJ 5-6	6°	±0.4	0.4
GJ 1.5-3	3°	±0.3	0.2	GJ 6-6	6°	±0.4	0.5
GJ 2-3	3°	±0.3	0.2	GJ 8-8	5°	±0.5	0.5
GJ 2-2	4°	±0.3	0.3	GJ 10-10	5°	±0.4	0.5
GJ 3-3	5°	±0.3	0.4	GJK 9.53	4°	±0.4	0.5
GJ 4-4	6°	±0.4	0.4	GJK 10-10	4°	±0.4	0.5
				GJK 12-12	4°	±0.5	0.5

Custom bore sizes available upon request

ORDERING INSTRUCTIONS

**GJ - XXX - XXX**



**CUI Inc.**  
 9615 SW Allen Blvd. #103  
 Beaverton, OR 97005  
 Tel: 503/643-4899 FAX: 503/643-6129

DRAWN BY JAS	UPDATED 07/02/02	CHECKED 07/02/02	RELEASED
-----------------	---------------------	---------------------	----------

PART NO.	<b>GJ Couplings</b>	REV. <b>A</b>
----------	---------------------	------------------