





9615 SW Allen, Suite 103  
 Beaverton, OR 97005  
 Phone: (503) 643-4899  
 800-275-4899  
 Fax: (503) 372-1266  
 Website: [www.cui.com](http://www.cui.com)

# Specifications

1	Part No.	GA0661			
2	Nominal Size	66 mm.	2 1/4" inch		
3	Impedance	8Ω ± 15%	at	800 Hz.	1 V.
4	Resonance	320 Hz.±	64 Hz.	FO Hz.	1 V.
5	S.P. Level	87 dB/w ±	3 dB	0.3 w. 50 cm. average at	
6	Response	fo Hz.~	6K Hz.	MAX 10dB	700, 900, 1.2K, 1.4K Hz.
7	Crossover Freq.	Hz.	Hz.	dB/OCT	Net work
8	Input Power	Nominal Input	0.3 w.	Handling Capacity	0.5 w.
9	Operation	Must be normal at program source			0.3 w.
10	Buzz, Rattle, etc.	Must be normal at sine wave			1.54 v.
11	Flux Density	Gauss ± 10%			
12	Total Flux	Max well min			
13	Magnet	Size	13 x 10 mm	gr	oz
14	Total Weight				gr oz
15	Load Test	After test meet item 9 and 10		White noise	0.3 W. 5 Hours
16	Distortion	% MAX			Hz W.
17	Heat Test	After test meet item 9 and 10		70±2 ±°C	20-50 %R.H. 5 Hours
18	Humidity Test	After test meet item 9 and 10		40±2 ±°C	90-95 %R.H. 5 Hours

PART NO.	GA0661	UNITS:	mm
DRAWN BY:	PAGE NO:	1 of 2	



9615 SW Allen, Suite 103  
Beaverton, OR 97005  
Phone: (503) 643-4899  
800-275-4899  
Fax: (503) 372-1266  
Website: [www.cui.com](http://www.cui.com)

TITLE:

PART NO.

GA0661

UNITS:

mm

DRAWN BY:

Page No.

2 of 2