





CUI STACK

9615 SW Allen, Suite 103
 Beaverton, OR 97005
 Phone: (503) 643-4899
 800-275-4899
 Fax: (503) 372-1266
 Website: www.cuistack.com

Specifications

| | | | | | |
|----|--------------------|---------------------------------------|---------------------|-----------------------|------------|
| 1 | Part No. | GA0771 | | | |
| 2 | Nominal Size | 77 mm. | 3" | inch | |
| 3 | Impedance | 8 $\Omega \pm 15\%$ | at | 800 Hz. | 1 V. |
| 4 | Resonance | 100 Hz. \pm 38 Hz. | | F0 Hz. | 1 V. |
| 5 | S.P. Level | 90 dB/w \pm 3 dB | | 1 w. 50 cm. | average at |
| 6 | Response | fo Hz. \sim 3.2K Hz. | MAX 10dB | 500, 800, 900, 1K Hz. | |
| 7 | Crossover Freq. | Hz. | Hz. | dB/OCT | Net work |
| 8 | Input Power | Nominal Input | 1 w. | Handling Capacity | 2 w. |
| 9 | Operation | Must be normal at program source 1 w. | | | |
| 10 | Buzz, Rattle, etc. | Must be normal at sine wave 2.83 v. | | | |
| 11 | Flux Density | Gauss \pm 10% | | | |
| 12 | Total Flux | Max well min | | | |
| 13 | Magnet | Size | 13 x 10 mm | gr | oz |
| 14 | Total Weight | gr oz | | | |
| 15 | Load Test | After test meet item 9 and 10 | White noise | 1 W. | 5 Hours |
| 16 | Distortion | % MAX Hz W. | | | |
| 17 | Heat Test | After test meet item 9 and 10 | 70 \pm 2 \pm °C | 20-50 %R.H. | 5 Hours |
| 18 | Humidity Test | After test meet item 9 and 10 | 40 \pm 2 \pm °C | 90-95 %R.H. | 5 Hours |

| | | | |
|-----------|--------|----------|--------|
| PART NO. | GA0771 | UNITS: | mm |
| DRAWN BY: | | PAGE NO: | 1 of 2 |



CUI STACK

9615 SW Allen, Suite 103
Beaverton, OR 97005
Phone: (503) 643-4899
800-275-4899
Fax: (503) 643-6129
Website: www.cuistack.com

| | |
|-----------|----------|
| TITLE: | |
| PART NO. | UNITS: |
| GA0771 | mm |
| DRAWN BY: | Page No. |
| | 2 of 2 |