



PART NUMBER: MEH9

DESCRIPTION: incremental encoder

ELECTRICAL SPECIFICATIONS

output waveform	Square Wave
output signals	A, B, Z phase
current consumption	≤40 mA
frequency response	0~100 KHz
output phase difference	A, B phase difference 90° ± 45° (T/4±T/8) Z phase T±T/2 (see output waveform)
supply voltage	5 V dc ± 10%
output resolution (ppr)	100, 200, 256, 300, 360, 500, 1000
waveform rise/fall time	2μ or less (outout cable 140mm or less)

MECHANICAL SPECIFICATIONS

max shaft load, radial:	1.9N (200gf)	0.98N (100gf) (1000 ppr)
axial:	1.9N (200gf)	0.98N (100gf) (1000 ppr)
starting torque	1 x 10 ⁻³ N·m (10 gf·cm max.)	
max rotational speed	6000 RPM	
shock resistance	500 m/s ² (50G), 3 times each on XYZ	
vibration proof	55 Hz, double amplitude 1.5mm, 2 hours each on XYZ	
weight	10g (with 140mm cable)	
cable	Vinyl wire (AWG 30) 140mm cable	

ENVIRONMENTAL SPECIFICATIONS

operating temp	0° to +60° C
storage temp	-20° to +80° C
humidity	RH 35%~90% non collecting

ORDERING INSTRUCTIONS

MEH9 - XXXPX

Resolution (PPR):
 100 = 100 PPR 300 = 300 PPR
 200 = 200 PPR 360 = 360 PPR
 256 = 256 PPR 500 = 500 PPR
 1000 = 1000 PPR


Output Circuit:
 "no entry" = TTL voltage output
 C = Open collector output

PART NUMBER: MEH9


DESCRIPTION: incremental encoder

CIRCUIT CONNECTIONS


Voltage Output



Open Collector Output






OUTPUT WAVEFORM



The position of Z phase against A, B phase is not specified

REV.	DESCRIPTION	DATE
A	NEW DRAWING	7/27/2007



TOLERANCE:
±0.3mm UNLESS OTHERWISE
SPECIFIED



20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

TITLE:	Incremental Encoder	REV:	A
PART NO:	MEH9	UNITS:	MM [INCHES]
DRAWN BY:	JMS	APPROVED BY:	
SCALE:			2:1

Cable Color	Red	White	Green	Yellow	Black	-	-	-
Output Type	Power	A-Phase	B-Phase	Z-Phase	0V	-	-	-

PC FILE NAME: MEH9
COPYRIGHT 2007 BY CUI INC.