

Specifications

1	Part No.	GF0571H			
2	Nominal Size	57 mm.	2 - 1/4" inch		
3	Impedance	8 Ω \pm 15%	at	800 Hz.	1 V.
4	Resonance	400 Hz. \pm 80 Hz.	F0 Hz.	1 V.	
5	S.P. Level	91 dB/w \pm 3 dB	1 w.	50 cm.	average at
6	Response	fo Hz. \sim 8.5K Hz.	MAX 10dB	1K, 1.4K, 1.7K, 2K Hz.	
7	Crossover Freq.	Hz.	Hz.	dB/OCT	Net work
8	Input Power	Nominal Input	1 w.	Handling Capacity	2 w.
9	Operation	Must be normal at program source			1 w.
10	Buzz, Rattle, etc.	Must be normal at sine wave			2.83 v.
11	Flux Density	Gauss \pm 10%			
12	Total Flux	Max well min			
13	Magnet	Size	32 x 18 x 6 mm	gr	oz
14	Total Weight	gr oz			
15	Load Test	After test meet item 9 and 10	White noise	1 W.	48 Hours
16	Distortion	% MAX		Hz	W.
17	Heat Test	After test meet item 9 and 10	70 \pm 2 \pm °C	20-50 %R.H.	48 Hours
18	Humidity Test	After test meet item 9 and 10	40 \pm 2 \pm °C	90-95 %R.H.	48 Hours

PART NO.

GF0571H



UNITS:

mm

DRAWN BY:

Page No:

1 of 2



9615 SW Allen, Suite 103
Beaverton, OR 97005
Phone: (503) 643-4899
800-275-4899
Fax: (503) 372-1266
Website: www.cui.com

TITLE:

PART NO.

GF0571H

UNITS:

mm

DRAWN BY:

Page No.

2 of 2