

Specifications

1	Part No.	GF0571H						
2	Nominal Size	57 mm.		2 - 1/4" inch				
3	Impedance	8 Ω	\pm	15%	at	800 Hz.	1 V.	
4	Resonance	400 Hz.	\pm	80 Hz.	F0 Hz.	1 V.		
5	S.P. Level	91 dB/w	\pm	3 dB	1 w.	50 cm. average at		
6	Response	fo Hz.	\sim	8.5K Hz.	MAX 10dB	1K, 1.4K, 1.7K, 2K Hz.		
7	Crossover Freq.	Hz.		Hz.		dB/OCT	Net work	
8	Input Power	Nominal Input		1 w.	Handling Capacity		2 w.	
9	Operation	Must be normal at program source					1	w.
10	Buzz, Rattle, etc.	Must be normal at sine wave					2.83	v.
11	Flux Density	Gauss \pm 10%						
12	Total Flux	Max well min						
13	Magnet	Size	32 x 18 x 6	mm	gr	oz		
14	Total Weight	gr						oz
15	Load Test	After test meet item 9 and 10		White noise	1 W.	48 Hours		
16	Distortion	% MAX		Hz	W.			
17	Heat Test	After test meet item 9 and 10		70 \pm 2	\pm °C	20-50 %R.H.	48 Hours	
18	Humidity Test	After test meet item 9 and 10		40 \pm 2	\pm °C	90-95 %R.H.	48 Hours	

PART NO.

GF0571H



UNITS:

mm

DRAWN BY:

Page No:

1 of 2



9615 SW Allen, Suite 103
 Beaverton, OR 97005
 Phone: (503) 643-4899
 800-275-4899
 Fax: (503) 372-1266
 Website: www.cui.com

TITLE:	
PART NO. GF0571H	UNITS: mm
DRAWN BY:	Page No. 2 of 2