



# Specifications

|    |                    |                                  |                        |             |          |
|----|--------------------|----------------------------------|------------------------|-------------|----------|
| 1  | Part No.           | GF1603B                          |                        |             |          |
| 2  | Nominal Size       | 160 mm.                          | 6 1/2"                 | inch        |          |
| 3  | Impedance          | 4Ω ± 15%                         | at 350 Hz.             | 1 V.        |          |
| 4  | Resonance          | 100 Hz.± 20 Hz.                  | FO Hz.                 | 1 V.        |          |
| 5  | S.P. Level         | 96 dB/w ± 2 dB                   | 1 w. 50 cm. average at |             |          |
| 6  | Response           | fo Hz.~ 20K Hz. MAX 10dB         | 300, 400, 500, 600 Hz. |             |          |
| 7  | Crossover Freq.    | Hz. Hz.                          | dB/OCT                 | Net work    |          |
| 8  | Input Power        | Nominal Input 8 w.               | Handling Capacity      | 10 w.       |          |
| 9  | Operation          | Must be normal at program source |                        | 8 w.        |          |
| 10 | Buzz, Rattle, etc. | Must be normal at sine wave      |                        | 4.5 v.      |          |
| 11 | Flux Density       | Gauss ± 10%                      |                        |             |          |
| 12 | Total Flux         | Max well min                     |                        |             |          |
| 13 | Magnet             | Size 70 x 32 x 10 mm             | gr                     | oz          |          |
| 14 | Total Weight       | gr oz                            |                        |             |          |
| 15 | Load Test          | After test meet item 9 and 10    | White noise            | 8 W.        | 24 Hours |
| 16 | Distortion         | % MAX                            |                        | Hz          | W.       |
| 17 | Heat Test          | After test meet item 9 and 10    | 70±2 ±°C               | 20-50 %R.H. | 24 Hours |
| 18 | Humidity Test      | After test meet item 9 and 10    | 40±2 ±°C               | 90-95 %R.H. | 24 Hours |

PART NO.

GF1603B



UNITS:

mm

DRAWN BY:

PAGE NO:

1 of 2



9615 SW Allen, Suite 103  
 Beaverton, OR 97005  
 Phone: (503) 643-4899  
 800-275-4899  
 Fax: (503) 372-1266  
 Website: [www.cui.com](http://www.cui.com)

TITLE:

PART NO.

GF1603B

UNITS:

mm

DRAWN BY:

Page No.

2 of 2