



Declaration of Conformity

Manufacturer:
CUI Inc
20050 SW 112th Ave
Tualatin, OR 97062

For the following equipment:

DC-DC Converter
CUI Series: PST50W
Models: 36V nominal input, see next page

This declaration of conformity is issued under the sole responsibility of the manufacturer. The object of the declaration described above is in conformity with the relevant UK designated legislations (and their amendments) and relevant designated standards or other technical specifications.

UK SI 2016 no. 1101: The Electrical Equipment (Safety) Regulations 2016 for Electrical Equipment Used within Certain Voltage Limits - as amended in 2019, 2020

UK SI 2016 no. 1091: The Electromagnetic Compatibility Regulations 2016 - as amended in 2019, 2020

UK SI 2012 no. 3032: The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 - as amended in 2019, 2020

References to the used, including the date of the standard, or references to the other technical specifications, including the date of the specification, in relation to which conformity is declared:

Health & Safety	BS EN IEC 62368-1:2020+A11:2020, IEC 62368-1:2018
EMC	BS EN 55032:2015+A11:2020; BS EN 55035:2017+A11:2020; BS EN50121-3-2:2016
RoHS	BS EN IEC 63000:2018

Approved by:



(manufacturer)

Editha Vergara
Global Director, Safety, Environmental

Tualatin, Oregon, USA

(place)

10/31/2023

(date)

UK Representative:



(manufacturer)

Cliff Gore
European Sales Director
Bel Power Solutions

Maidstone, UK

(place)

10/31/2023

(date)

MODEL LIST

PST50W-36-SXXB, PST50W-36-SXXBN, PST50W-36-SXXB-O, PST50W-36-SXXBN-O, PST50W-36-SXXB-H, PST50W-36-SXXBN-H, PST50W-36-SXXB-H-DIN, PST50W-36-SXXBN-H-DIN (where XX = 12, 15, 24, 28, 48 denote output voltage)

Model	Input voltage (typ.)	Input voltage (range)	Output voltage (Vdc)
PST50W-36-S12B	36	9.5-75	12
PST50W-36-S15B	36	9.5-75	15
PST50W-36-S24B	36	9.5-75	24
PST50W-36-S28B	36	9.5-75	28
PST50W-36-S48B	36	9.5-75	48
PST50W-36-S12BN	36	9.5-75	12
PST50W-36-S15BN	36	9.5-75	15
PST50W-36-S24BN	36	9.5-75	24
PST50W-36-S28BN	36	9.5-75	28
PST50W-36-S48BN	36	9.5-75	48
PST50W-36-S12B-O	36	9.5-75	12
PST50W-36-S15B-O	36	9.5-75	15
PST50W-36-S24B-O	36	9.5-75	24
PST50W-36-S28B-O	36	9.5-75	28
PST50W-36-S48B-O	36	9.5-75	48
PST50W-36-S12BN-O	36	9.5-75	12
PST50W-36-S15BN-O	36	9.5-75	15
PST50W-36-S24BN-O	36	9.5-75	24
PST50W-36-S28BN-O	36	9.5-75	28
PST50W-36-S48BN-O	36	9.5-75	48
PST50W-36-S12B-H	36	9.5-75	12
PST50W-36-S15B-H	36	9.5-75	15
PST50W-36-S24B-H	36	9.5-75	24
PST50W-36-S28B-H	36	9.5-75	28
PST50W-36-S48B-H	36	9.5-75	48
PST50W-36-S12BN-H	36	9.5-75	12
PST50W-36-S15BN-H	36	9.5-75	15
PST50W-36-S24BN-H	36	9.5-75	24
PST50W-36-S28BN-H	36	9.5-75	28
PST50W-36-S48BN-H	36	9.5-75	48
PST50W-36-S12B-H-DIN	36	9.5-75	12
PST50W-36-S15B-H-DIN	36	9.5-75	15
PST50W-36-S24B-H-DIN	36	9.5-75	24
PST50W-36-S28B-H-DIN	36	9.5-75	28
PST50W-36-S48B-H-DIN	36	9.5-75	48
PST50W-36-S12BN-H-DIN	36	9.5-75	12
PST50W-36-S15BN-H-DIN	36	9.5-75	15
PST50W-36-S24BN-H-DIN	36	9.5-75	24
PST50W-36-S28BN-H-DIN	36	9.5-75	28
PST50W-36-S48BN-H-DIN	36	9.5-75	48

REVISION HISTORY

rev.	description	date
1.0	initial release	10/31/23

The revision history provided is for informational purposes only and is believed to be accurate.