



PART NUMBER: MES30

DESCRIPTION: incremental encoder

ELECTRICAL SPECIFICATIONS

output waveform	Square Wave
output signals	A, B, Z phase
current consumption	≤50 mA
frequency response	0~100 KHz
output phase difference	A, B phase difference 90° ± 45° (T/4±T/8) Z phase T±T/2 (see output waveform)
supply voltage	5 V dc ± 10% (line driver output only), 5 ~ 12 V dc ± 10%, 24 V dc ± 10% (open collector output only)
output resolution (ppr)	40, 50, 60, 100, 200, 250, 300, 360, 400, 450, 500, 512, 600, 720, 800, 900, 1000, 1024, 1200, 1500, 1800, 2000, 2048, 2500, 3600, 4500, 9000
waveform rise/fall time	2μ or less (output cable 1m or less)

MECHANICAL SPECIFICATIONS

max shaft load, radial:	19.6N (2kgf)	14.7N (1.5kgf) (800-9000 ppr)
axial:	9.8N (1kgf)	4.9N (0.5kgf) (800-9000 ppr)
starting torque	2 x 10 ⁻³ N·m (20 gf·cm)	
max rotational speed	6000 RPM	
shock resistance	500 m/s ² (50G), 3 times each on XYZ	
vibration proof	55 Hz, double amplitude 1.5mm, 2 hours each on XYZ	
weight	70g (with 1m cable)	
cable	4.2mm outside diameter, 5 core vinyl wire insulated shield cable (1m)	

ENVIRONMENTAL SPECIFICATIONS

operating temp	-10° to +70° C
storage temp	-20° to +80° C
humidity	RH 35%~90% non collecting

ORDERING INSTRUCTIONS


MES30 - XXXXP-XX

	Resolution (PPR):		Output Circuit:		Input Voltage:
40 = 40 PPR	450 = 450 PPR	1200 = 1200 PPR	"no entry" = TTL voltage output		1 = 5V dc ± 10%
50 = 50 PPR	500 = 500 PPR	1500 = 1500 PPR	C = Open collector output		(line driver output only)
60 = 60 PPR	512 = 512 PPR	1800 = 1800 PPR	E = Line driver output		3 = 5 ~ 12V dc ± 10%
100 = 100 PPR	600 = 600 PPR	2000 = 2000 PPR			4 = 24V dc ± 10%
200 = 200 PPR	720 = 720 PPR	2048 = 2048 PPR			(open collector output only)
250 = 250 PPR	800 = 800 PPR	2500 = 2500 PPR			
300 = 300 PPR	900 = 900 PPR	3600 = 3600 PPR			
360 = 360 PPR	1000 = 1000 PPR	4500 = 4500 PPR			
400 = 400 PPR	1024 = 1024 PPR	9000 = 9000 PPR			


PART NUMBER: MES30

DESCRIPTION: incremental encoder

CIRCUIT CONNECTIONS







OUTPUT WAVEFORM



The position of Z phase against A, B phase is not specified

REV.	DESCRIPTION	DATE
A	NEW DRAWING	7/30/2007



TOLERANCE:
±0.3mm UNLESS OTHERWISE
SPECIFIED



CUI INC

20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-612-2300
800-275-4899
Fax: 503-612-2383
Website: www.cui.com

TITLE: Incremental Encoder
REV: A

PART NO: MES30
UNITS: MM [INCHES]

DRAWN BY: JMS
APPROVED BY: [Signature]
SCALE: 1:1

Cable Color	Red	White	Green	Yellow	Black	-	-	-
Output Type	Power	A-Phase	B-Phase	Z-Phase	0V	-	-	-

COPYRIGHT 2007
BY CUI INC.

PC FILE NAME: MES30