



PART NUMBER: SEH17

DESCRIPTION: sine wave encoder

ELECTRICAL SPECIFICATIONS

output waveform	Sine Wave
output signals	A phase, A,B phase
current consumption	≤30 mA
frequency response	0~20 KHz
output phase difference	A, B phase difference 90° ± 45°
supply voltage	5 V dc ± 10%
output resolution (ppr)	100, 200, 300, (360) (single phase only)

MECHANICAL SPECIFICATIONS

max shaft load, radial:	1.9Nm (200gf) (2); 4.9Nm (500gf) (4)
axial:	1.9Nm (200gf) (2); 4.9Nm (500gf) (4)
starting torque	0.3 x 10 ⁻³ N·m (3 gf·cm)
max rotational speed	6000 RPM
shock resistance	500m/s ² (50G), 11ms, 3 times each on XYZ
vibration proof	55 Hz, 1.5mm, 2 hours each on XYZ
weight	20g (with 130mm cable)
cable	Vinyl wire (AWG28) 130mm

ENVIRONMENTAL SPECIFICATIONS

operatingtemp	0° to +50° C
storage temp	-20° to +80° C
humidity	90% max. non collecting

ORDERING INSTRUCTIONS


SEH17 - XXXXX

Resolution (PPR):	Output Phase:
100 = 100 PPR	A = Single Phase
200 = 200 PPR	AB = Two-Phase
300 = 300 PPR	
360 = 360 PPR	

PART NUMBER: SEH-17

DESCRIPTION: sine wave encoder

CIRCUIT CONNECTIONS



OUTPUT WAVEFORM

Clockwise rotation viewed from front

