

**PART NUMBER:** VAS3 series**DESCRIPTION:** DC/DC converter**features**

- 3W isolated output
- efficiency to 61%
- regulated outputs
- LC input filter
- low ripple and noise
- 24-pin DIP package



model number <sup>1</sup>	input voltage	output voltage	output current	input current		efficiency
				no load	full load	
VAS3-S5-S5	5 Vdc	5 Vdc	600 mA	120 mA	984 mA	61%
VAS3-S5-S12	5 Vdc	12 Vdc	250 mA	120 mA	984 mA	61%
VAS3-S5-S15	5 Vdc	15 Vdc	200 mA	120 mA	984 mA	61%
VAS3-S5-D12	5 Vdc	±12 Vdc	±125 mA	120 mA	984 mA	61%
VAS3-S5-D15	5 Vdc	±15 Vdc	±100 mA	120 mA	984 mA	61%
VAS3-S12-S5	12 Vdc	5 Vdc	600 mA	60 mA	410 mA	61%
VAS3-S12-S12	12 Vdc	12 Vdc	250 mA	60 mA	410 mA	61%
VAS3-S12-S15	12 Vdc	15 Vdc	200 mA	60 mA	410 mA	61%
VAS3-S12-D12	12 Vdc	±12 Vdc	±125 mA	60 mA	410 mA	61%
VAS3-S12-D15	12 Vdc	±15 Vdc	±100 mA	60 mA	410 mA	61%
VAS3-S24-S5	24 Vdc	5 Vdc	600 mA	40 mA	205 mA	61%
VAS3-S24-S12	24 Vdc	12 Vdc	250 mA	40 mA	205 mA	61%
VAS3-S24-S15	24 Vdc	15 Vdc	200 mA	40 mA	205 mA	61%
VAS3-S24-D12	24 Vdc	±12 Vdc	±125 mA	40 mA	205 mA	61%
VAS3-S24-D15	24 Vdc	±15 Vdc	±100 mA	40 mA	205 mA	61%
VAS3-S28-S5	28 Vdc	5 Vdc	600 mA	35 mA	176 mA	61%
VAS3-S28-S12	28 Vdc	12 Vdc	250 mA	35 mA	176 mA	61%
VAS3-S28-S15	28 Vdc	15 Vdc	200 mA	35 mA	176 mA	61%
VAS3-S28-D12	28 Vdc	±12 Vdc	±125 mA	35 mA	176 mA	61%
VAS3-S28-D15	28 Vdc	±15 Vdc	±100 mA	35 mA	176 mA	61%
VAS3-S48-S5	48 Vdc	5 Vdc	600 mA	20 mA	102 mA	61%
VAS3-S48-S12	48 Vdc	12 Vdc	250 mA	20 mA	102 mA	61%
VAS3-S48-S15	48 Vdc	15 Vdc	200 mA	20 mA	102 mA	61%
VAS3-S48-D12	48 Vdc	±12 Vdc	±125 mA	20 mA	102 mA	61%
VAS3-S48-D15	48 Vdc	±15 Vdc	±100 mA	20 mA	102 mA	61%

**NOTES:**

1. suffix "-SMT" for SMT case style

**PART NUMBER:** VAS3 series**DESCRIPTION:** DC/DC converter**INPUT**

input voltage range	±10%
input filter	LC type

**OUTPUT**

voltage accuracy	±3.0% max.
temperature coefficient	±0.02% / °C max.
ripple and noise, 20MHz BW	50mV p-p max.
short circuit protection	indefinite & current limit
line Regulation <sup>1</sup>	single/dual
	±0.3%
load Regulation <sup>2</sup>	single
	±0.5%
	dual
	±1.0%

**GENERAL SPECIFICATIONS**

efficiency	see table
isolation capacitance	150 pF typ.
isolation resistance	10 <sup>9</sup> Ohms
switching frequency	80K Hz min.
operating temperature range	-25°C to +71°C
storage temperature range	-40°C to +100°C
case temperature	100°C max.
cooling	free air convection
dimensions	1.25x0.8x0.4 inches (31.8x20.3x10.2mm)

**ISOLATION VOLTAGE**

500 Vdc min	standard models
-------------	-----------------

**CASE MATERIAL**

standard models	black coated copper with non-conductive base
-----------------	--

**NOTES:**


1. measured from high line to low line
2. measured from full load to 10% load

**PART NUMBER:** VAS3 series

**DESCRIPTION:** DC/DC converter

## DIMENSIONS (mm)

NOTE: Pin Size is 0.02" Inch (0.5mm) DIA  
All Dimensions In Inches(mm)  
Tolerance .xx= ±.02, .xxx= ±.010



PIN CONNECTION		
500 VDC		
Pin	Single Output	Dual Output

1	24	+V Input	+V Input
2	23	NC	-V Output
3	22	NC	Common
10	-V Output	Common	
11	+V Output	+V Output	
12	-V Input	-V Input	
13	-V Input	-V Input	
14	+V Output	+V Output	
15	-V Output	Common	

\*NC-NO CONNECTION WITH PIN

## DERATING CURVE

