

**SERIES:** VF-D250-DXXA | **DESCRIPTION:** AC-DC POWER SUPPLY

**FEATURES**


- up to 250 W continuous power w/ 16 CFM forced air
- 600 W peak power within 500  $\mu$ s duty duration
- passive power correction
- dual outputs
- power good signal
- remote on/off control
- 3,000 Vac isolation voltage
- over load, over voltage, over temperature, and short circuit protections
- UL/cUL, and TUV 60950-1 safety approvals
- efficiency up to 70%



| MODEL          | output voltage | output current |                                 | output power <sup>1</sup> |                                 | ripple and noise <sup>3,4</sup> | efficiency |
|----------------|----------------|----------------|---------------------------------|---------------------------|---------------------------------|---------------------------------|------------|
|                | (Vdc)          | max (A)        | max w/ airflow <sup>2</sup> (A) | max (W)                   | max w/ airflow <sup>2</sup> (W) | max (mVp-p)                     | typ (%)    |
| VF-D250-D312A  | 3.3            | 12             | 24                              | 100                       | 200                             | 50                              | 70%        |
|                | 12             | 7              | 12                              |                           |                                 |                                 |            |
| VF-D250-D324A  | 3.3            | 12             | 24                              | 100                       | 200                             | 50                              | 70%        |
|                | 24             | 4              | 6                               |                           |                                 |                                 |            |
| VF-D250-D512A  | 5              | 12             | 24                              | 100                       | 200                             | 50                              | 70%        |
|                | 12             | 7              | 12                              |                           |                                 |                                 |            |
| VF-D250-D524A  | 5              | 12             | 24                              | 100                       | 200                             | 50                              | 70%        |
|                | 24             | 4              | 6                               |                           |                                 |                                 |            |
| VF-D250-D548A  | 5              | 12             | 24                              | 100                       | 200                             | 50                              | 70%        |
|                | 48             | 2              | 3                               |                           |                                 |                                 |            |
| VF-D250-D1224A | 12             | 7              | 12                              | 135                       | 250                             | 120                             | 70%        |
|                | 24             | 4              | 6                               |                           |                                 |                                 |            |

- Notes:
1. Maximum total combined power
  2. With external 16 CFM fan
  3. 10% minimum load is required to maintain the ripple and regulation.
  4. Ripple and noise is measured from 10 KHz to 20 MHz at output terminals with a 0.1  $\mu$ F ceramic capacitor and a 22  $\mu$ F electrolytic capacitor in parallel.

**PART NUMBER KEY**



## INPUT

| parameter      | conditions/description  | min    | typ | max      | units  |
|----------------|---|--------|-----|----------|--------|
| voltage        | 90-132/180-264 auto selectable  | 90/180 |     | 132/264  | Vac    |
| frequency      |   | 47     |     | 63       | Hz     |
| current        | at 110~120 Vac, cold start<br>at 200~240 Vac, cold start                            |        |     | 6<br>3   | A<br>A |
| inrush current | at 115 Vac, full load, cold start<br>at 230 Vac, full load, cold start              |        |     | 35<br>70 | A<br>A |
| power factor   | compliant to EN 61000-3-2 class A   |        |     |          |        |
| remote on/off  | designated as RMSW on the CN1, requires a low signal to inhibit output, hiccup mode |        |     |          |        |

## OUTPUT

| parameter               | conditions/description  | min | typ  | max | units |
|-------------------------|---|-----|------|-----|-------|
| line regulation         | low line to high line   |     | ±5   |     | %     |
| load regulation         | all other outputs   |     | ±5   |     | %     |
| temperature coefficient |   |     | 0.25 |     | mV/°C |
| transient response      | Output voltage returns to within 1% in less than 2.5 ms for a 50% load change.<br>Peak transient does not exceed 5%.  |     |      |     |       |
| start-up time           | at 120 Vac  |     |      | 1   | s     |
| rise time               |   | 0.2 |      | 20  | ms    |
| hold-up time            | at 120 Vac and 80% of rated maximum load  | 20  |      |     | ms    |
| adjustability           |   |     | ±5   |     | %     |
| power good              | Designated as PG on the CN1.<br>This signal goes high 100-500 mS after the output reaches regulation.<br>It goes low at least 1 mS before loss of regulation. |     |      |     |       |
| fan drive               | 12 Vdc / 400 mA for external fan  |     |      |     |       |

## PROTECTIONS

| parameter                   | conditions/description  | min | typ | max | units |
|-----------------------------|---|-----|-----|-----|-------|
| over voltage protection     | AC input needs to be reset to restart the power supply                        |     |     | 130 | %     |
| over current protection     | automatically recovers  |     | 110 | 140 | %     |
| short circuit protection    | short circuit can be continuous, recovers automatically upon removal of short |     |     |     |       |
| over temperature protection | auto recovery   |     |     | 85  | °C    |

## SAFETY & COMPLIANCE


| parameter         | conditions/description   | min                     | typ | max             | units             |
|-------------------|--|-------------------------|-----|-----------------|-------------------|
| isolation voltage | applied for 3 seconds at 10 mA max.<br>primary to secondary<br>primary to transformer core<br>primary to earth chassis | 3,000<br>1,500<br>1,500 |     |                 | Vac<br>Vac<br>Vac |
| safety approvals  | UL 60950-1, CSA C22.2 No. 60950-1, TUV EN 60950-1 and CB   |                         |     |                 |                   |
| EMI/EMC           | CISPR 22/EN 55022 class B, EN 61000-3-2, 3,<br>EN 61000-4-2, 3, 4, 5, 6, 8, 11, EN 55024 CE marked (LVD)               |                         |     |                 |                   |
| leakage current   | standard model at 264 Vac<br>low-leakage model at 240 Vac<br>low-leakage model at 120 Vac                              |                         |     | 1<br>500<br>300 | mA<br>µA<br>µA    |
| RoHS compliant    | yes  |                         |     |                 |                   |
| MTBF              | according to MIL-HDBK-217 at 30 °C   | 100,000                 |     |                 | hrs               |

## ENVIRONMENTAL

| parameter             | conditions/description                               | min | typ | max | units |
|-----------------------|--|-----|-----|-----|-------|
| operating temperature |  | 0   |     | 50  | °C    |
| storage temperature   |  | -20 |     | 85  | °C    |
| operating humidity    | non-condensing                                       | 5%  |     | 90% | %     |
| storage humidity      |  | 5%  |     | 95% | %     |
| vibration             | acceleration $\pm 7.35 M/(SxS)$ , on X, Y and Z Axis | 5   |     | 50  | Hz    |

## DERATING CURVES


output power vs. ambient temperature



## MECHANICAL

| parameter  | conditions/description | min | typ | max | units  |
|------------|------------------------|-----|-----|-----|--------|
| dimensions | 5(L) x 3.2(W) x 1.5(H) |     |     |     | inches |
| weight     |                        |     |     | 450 | g      |

## MECHANICAL DRAWING



- Notes:
1. CN1 mates with molex part no. 09-91-0500 or equivalent and molex 2478, 2578, 8818 crimp pins.
  2. CN2 mates with molex part no. 09-91-0800 and molex 2478, 2578, 8818 crimp pins.
  3. CN3 mates with JST part no. XHP-3 or equivalent (CHYAO SHIUNN JS-2001-03) and JST SXH-002T-P0.6 mating pins
  4. Fan drive connector mates with JST part no. XHP-2 or equivalent (CHYAO SHIUNN JS-2001-02).
  5. Mounting hole max depth 2.30mm

## REVISION HISTORY

| rev. | description                 | date       |
|------|-----------------------------|------------|
| 1.0  | initial release             | 05/05/2009 |
| 1.01 | new template applied        | 12/17/2011 |
| 1.02 | V-Infinity branding removed | 08/28/2012 |
| 1.03 | updated spec                | 03/29/2013 |
| 1.04 | updated spec                | 01/19/2018 |

The revision history provided is for informational purposes only and is believed to be accurate.



**CUI INC**<sup>®</sup>

**Headquarters**  
20050 SW 112th Ave.  
Tualatin, OR 97062  
**800.275.4899**

Fax 503.612.2383  
**cui.com**  
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.