

SERIES: VQB100R | **DESCRIPTION:** DC-DC CONVERTER

FEATURES


- up to 100 W isolated output
- industry standard quarter brick package
- 3:1 input range (66~160 Vdc)
- single output from 5~24 Vdc
- 2,250 Vdc isolation
- over current, over temperature, over voltage, and short circuit protections
- remote on/off
- efficiency up to 92%



| MODEL | input voltage range | output voltage | output current max | output power max | ripple and noise ¹ max | efficiency typ |
|------------------|---------------------|----------------|--------------------|------------------|-----------------------------------|----------------|
| | (Vdc) | (Vdc) | (A) | (W) | (mVp-p) | (%) |
| VQB100R-T110-S5 | 66 ~ 160 | 5 | 20 | 100 | 100 | 90 |
| VQB100R-T110-S12 | 66 ~ 160 | 12 | 8.4 | 100 | 150 | 92 |
| VQB100R-T110-S24 | 66 ~ 160 | 24 | 4.2 | 100 | 240 | 91 |

Notes: 1. ripple and noise are measured at 20 MHz BW with 10µF tantalum capacitor and 1µF ceramic capacitor across output
 2. an external input capacitor of 120 µF is recommended to reduce the input ripple voltage.

PART NUMBER KEY



INPUT

| parameter | conditions/description | min | typ | max | units |
|-------------------------|--|-----|-----|-----|-------|
| operating input voltage | | 66 | 110 | 160 | Vdc |
| input surge voltage | 100 ms max. | | | 180 | Vdc |
| under voltage lockout | power up | | 62 | | Vdc |
| | power down | | 56 | | Vdc |
| start-up time | | | 45 | | ms |
| filter | PI type | | | | |
| on/off ¹ | models ON (open circuit or 3.5~75 Vdc) | | | | |
| | models OFF (0~1.8 Vdc) | | | | |

Notes: 1. logic compatibility, open collector reference to -input.

OUTPUT

| parameter | conditions/description | min | typ | max | units |
|-------------------------|--------------------------------------|-----|-------|-----------|--------------|
| output capacitance | 5 Vdc output model | | | 10,000 | μF |
| | 12 Vdc output model | | | 8,800 | μF |
| | 24 Vdc output model | | | 1,500 | μF |
| line regulation | measured from high line to low line | | | ±0.2 | % |
| load regulation | measured from full load to zero load | | | ±0.2 | % |
| voltage accuracy | | | | ±1.5 | % |
| adjustability | see application notes | | ±10 | | % |
| switching frequency | 100% load, input voltage range | | 200 | | kHz |
| transient response | 25% step load change | | | ±5 200 | % Vout μs |
| temperature coefficient | | | ±0.03 | | %/°C |

PROTECTIONS

| parameter | conditions/description | min | typ | max | units |
|-----------------------------|--------------------------|-----|-----|-----|-------|
| over voltage protection | %Vo | 115 | | 140 | % |
| over current protection | % nominal output current | 110 | | 180 | % |
| short circuit protection | continuous | | | | |
| over temperature protection | | | 105 | | °C |

SAFETY AND COMPLIANCE

| parameter | conditions/description | min | typ | max | units |
|-----------------------|---|-------|-------|-----|-------|
| isolation voltage | input to output | 2,250 | | | Vdc |
| | input to case | 2,250 | | | Vdc |
| | output to case | 1,500 | | | Vdc |
| isolation resistance | | 10 | | | MΩ |
| isolation capacitance | | | 1,000 | | pF |
| safety approvals | UL 60950-1 | | | | |
| EMC | EN50155 (EN50121-3-2) (external circuit required, see Figure 1) | | | | |
| EMI | EN55011 Class A | | | | |
| | EN61000-4-2 Air ±8 kV Class B | | | | |
| ESD | EN61000-4-2 Contactr ±6 kV Class A | | | | |
| | | | | | |
| radiated immunity | EN61000-4-3 10 V/m Class A | | | | |
| EFT/burst | EN61000-4-4 ±2 kV Class A | | | | |
| surge | EN61000-4-5 ±1 kV Class B | | | | |
| conducted immunity | EN61000-4-6 10 Vr.m.s Class A | | | | |
| RoHS | 2011/65/EU | | | | |


ENVIRONMENTAL

| parameter | conditions/description | min | typ | max | units |
|----------------------------|--|-----|-----|-----|-------|
| operating case temperature | | -40 | | 100 | °C |
| storage temperature | | -55 | | 105 | °C |
| humidity | non-condensing | | | 95 | % |
| shock/vibration | EN50155 (EN61373) | | | | |
| enviromental | EN50155 (EN60068-2-1, EN60068-2-2, EN60068-2-30) | | | | |

SOLDERABILITY

| parameter | conditions/description | min | typ | max | units |
|----------------|----------------------------|-----|-----|-----|-------|
| wave soldering | see wave soldering profile | | | 260 | °C |

- Notes:
1. Soldering materials: Sn/Cu/Ni
 2. Ramp up rate during preheat: 1.4°C/s (from 50°C to 100°C)
 3. Soaking temperature: 0.5°C/s (from 100°C to 130°C), 60±20 seconds
 4. Peak temperature: 260°C, above 250°C for 3~6 seconds
 5. Ramp down rate during cooling: -10°C/s (from 260°C to 150°C)




MECHANICAL

| parameter | conditions/description | min | typ | max | units |
|---------------|---|-----|------|-----|-------|
| dimensions | 2.28 x 1.45 x 0.5 (57.9 x 36.8 x 12.7 mm) | | | | inch |
| case material | aluminum baseplate with plastic case | | | | |
| weight | | | 61.5 | | g |

MECHANICAL DRAWING

units: inches [mm]
 tolerance: x.xx ± 0.02" [±0.5mm]
 x.xxx ± 0.010" [±0.25mm]

| PIN CONNECTIONS | |
|-----------------|----------|
| PIN | FUNCTION |
| 1 | +Vin |
| 2 | On/Off |
| 3 | -Vin |
| 4 | -Vo |
| 5 | -S |
| 6 | TRIM |
| 7 | +S |
| 8 | +Vo |



EMC RECOMMENDED CIRCUITS

EN50155 [EN50121-3-2] (EN55011 Class A)

Figure 1
Recommended Circuit for EN50155 (EN50121-3-2) (EN55011 Class A)




Table 1

| Recommended External Circuit Components | | | | | | | |
|---|-------------------------|-------------------|-------------------|---------|---------|------|---------|
| Model | D1 | C1 | C2 | C3 | C4 | L1 | L2 |
| VQB100R-T110-S5 | 1.5KE180A Littelfuse | 220uF/200V YXF | 220uF/200V YXF | 2200 pF | 2200 pF | 5 μH | 0.33 mH |
| VQB100R-T110-S12 | 1.5KE180A Littelfuse | 220uF/200V YXF | 220uF/200V YXF | 2200 pF | 2200 pF | 5 μH | 0.33 mH |
| VQB100R-T110-S24 | 1.5KE180A Littelfuse | 220uF/200V YXF | 220uF/200V YXF | 2200 pF | 2200 pF | 5 μH | 0.33 mH |

Note: C1, C2 Aluminum Capacitors and C3, C4 Ceramic Capacitors

EN55022 Class B

Figure 2
Recommended Circuit for EN55022 Class B




Table 2

| Recommended External Circuit Components | | | | | | |
|---|---------------------|---------------------|---------|---------|------|---------|
| Model | C1 | C2 | C3 | C4 | L1 | L2 |
| VQB100R-T110-S5 | 220 μF/200 V YXF | 220 μF/200 V YXF | 2200 pF | 2200 pF | 5 μH | 0.33 mH |
| VQB100R-T110-S12 | 220 μF/200 V YXF | 220 μF/200 V YXF | 2200 pF | 2200 pF | 5 μH | 0.33 mH |
| VQB100R-T110-S24 | 220 μF/200 V YXF | 220 μF/200 V YXF | 2200 pF | 2200 pF | 5 μH | 0.33 mH |

Note: C1, C2 Aluminum Capacitors and C3, C4 Ceramic Capacitors


APPLICATION NOTES

1. Output Voltage Trimming

Leave open if not used.

Figure 3

Application Circuit for Trim pin



Formula for Trim Resistor

$$R_{trim - up} = \left(\frac{R_1(V_r - V_f(\frac{R_2}{R_2 + R_3}))}{V_o - V_{o, nom}} \right) - \frac{R_2 R_3}{R_2 + R_3} \text{ (k}\Omega\text{)}$$

$$R_{trim - down} = \frac{R_1(V_o - V_r)}{V_{o, nom} - V_o} - R_2 \text{ (k}\Omega\text{)}$$

Note: $R_{trim-up}$ is the external resistor in $k\Omega$
 $R_{trim-down}$ is the external resistor in $k\Omega$
 $V_{o, nom}$ is the nominal output voltage
 V_o is the desired output voltage
 $R_1, R_2, R_3,$ and V_r are internal (see Table 3).

Table 3

| Vout (Vdc) | R1 (k Ω) | R2 (k Ω) | R3 (k Ω) | Vr (V) | Vf (V) |
|------------|------------------|------------------|------------------|--------|--------|
| 5 | 2.32 | 3.3 | 0 | 2.5 | 0 |
| 12 | 9.1 | 51 | 5.1 | 2.5 | 0.46 |
| 24 | 20 | 100 | 7.5 | 2.5 | 0.46 |

REVISION HISTORY

| rev. | description | date |
|------|---|------------|
| 1.0 | initial release | 06/20/2012 |
| 1.01 | misc. updates, added product photo | 11/13/2012 |
| 1.02 | updated input voltage range and drawing | 01/29/2013 |
| 1.03 | updated spec | 03/18/2013 |
| 1.04 | updated features section | 05/30/2013 |
| 1.05 | added EMC recommendations | 06/18/2015 |

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.